

## BNC Male Right Angle to BNC Male Right Angle Low Loss Cable Using LMR-240-UF Coax with HeatShrink




### PE3W06076/HS

#### Configuration

- Connector 1: BNC Male Right Angle
- Connector 2: BNC Male Right Angle
- Cable Type: LMR-240-UF
- Coax Flex Type: Flexible

#### Features

- Max Frequency 4 GHz
- Shielding Effectivity > 90 dB
- 84% Phase Velocity
- Double Shielded
- TPE Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3W06076/HS BNC male right angle to BNC male right angle cable using LMR-240-UF coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack BNC to BNC cable assembly has a male to male gender configuration with 50 ohm flexible LMR-240-UF coax. The PE3W06076/HS BNC male to BNC male cable assembly operates to 4 GHz. The right angle BNC interfaces on the LMR-240-UF cable allow for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
VSWR			1.4:1	
Velocity of Propagation		84		%
RF Shielding	90			dB
Group Delay		1.21 [3.97]		ns/ft [ns/m]
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		4.28 [14.04]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		3.89 [12.76]		Ohms/1000ft [Ohms/Km]

## BNC Male Right Angle to BNC Male Right Angle Low Loss Cable Using LMR-240-UF Coax with HeatShrink



### PE3W06076/HS

#### Electrical Specifications

Description	Minimum	Typical					Maximum	Units
Jacket Spark						5,000		Vrms

#### Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	100	250	500	1000	4000	MHz	
PE3W06076/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.029	0.046	0.066	0.096	0.195	dB/ft	
			0.1	0.16	0.22	0.32	0.64	dB/m	
PE3W06076/HS-12	12 inch	Insertion Loss (Typ.)	0.43	0.45	0.47	0.5	0.6	dB	0.126
PE3W06076/HS-24	24 inch	Insertion Loss (Typ.)	0.46	0.5	0.54	0.6	0.79	dB	0.159
PE3W06076/HS-36	36 inch	Insertion Loss (Typ.)	0.49	0.54	0.6	0.69	0.99	dB	0.191
PE3W06076/HS-60	60 inch	Insertion Loss (Typ.)	0.55	0.63	0.73	0.88	1.38	dB	0.255
PE3W06076/HS-300	300 inch	Insertion Loss (Typ.)	1.13	1.55	2.05	2.8	5.28	dB	0.895

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.2 dB  
Loss due to Connector 2: 0.2 dB  
Base Weight: 0.126 pounds  
Additional Weight per Inch: 0.00267 pounds

#### Mechanical Specifications

##### Cable Assembly

Width/Diameter 0.5 in [12.7 mm]  
Weight 0.126 lbs [57.15 g]

##### Cable

Cable Type LMR-240-UF  
Impedance 50 Ohms  
Inner Conductor Type Stranded  
Inner Conductor Material and Plating Copper  
Dielectric Type PE (F)  
Number of Shields 2  
Shield Layer 1 Aluminum Tape  
Shield Layer 2 Tinned Copper Braid  
Jacket Material TPE, Black  
Jacket Diameter 0.24 in [6.1 mm]  
One Time Minimum Bend Radius 0.75 in [19.05 mm]  
Repeated Minimum Bend Radius 2.5 in [63.5 mm]  
Bending Moment 0.13 lbs-ft [0.18 N-m]  
Flat Plate Crush 13 lbs/in [0.23 Kg/mm]  
Tensile Strength 80 lbs [36.29 Kg]

BNC Male Right Angle to BNC Male Right Angle Low Loss Cable Using LMR-240-UF Coax with HeatShrink



## PE3W06076/HS

### Connectors

Description	Connector 1	Connector 2
Type	BNC Male Right Angle	BNC Male Right Angle
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Right Angle
Contact Material and Plating	Brass, Gold	Brass, Gold
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel

### Environmental Specifications

Operating Range Temperature -40 to +85 deg C

### Compliance Certifications

(see [product page](#) for current document)

### Plotted and Other Data

Notes:

## BNC Male Right Angle to BNC Male Right Angle Low Loss Cable Using LMR-240-UF Coax with HeatShrink




### PE3W06076/HS

#### Typical Performance Data

#### How to Order

Part Number Configuration:



Example: PE3W06076/HS-12 = 12 inches long cable  
PE3W06076/HS-100cm = 100 cm long cable

BNC Male Right Angle to BNC Male Right Angle Low Loss Cable Using LMR-240-UF Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC Male Right Angle to BNC Male Right Angle Low Loss Cable Using LMR-240-UF Coax with HeatShrink PE3W06076/HS](#)

URL: <https://www.pasternack.com/bnc-male-right-angle-to-bnc-male-low-loss-cable-using-lmr-240-uf-with-heatshrink-pe3w06076-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE3W06076/HS CAD Drawing

BNC Male Right Angle to BNC Male Right Angle Low Loss Cable Using LMR-240-UF Coax with HeatShrink

