

SMA Female to MCX Plug Right Angle Cable
60 Inch Length Using PE-SR405FLJ Coax




RF Cable Assemblies Technical Data Sheet

PE3W03859-60


Configuration

- Connector 1: SMA Female
- Connector 2: MCX Plug Right Angle
- Cable Type: PE-SR405FLJ



Features

- Max Frequency 6 GHz
- Shield Effectivity > 100 dB
- 69.5% Phase Velocity
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W03859-60 SMA female to MCX plug right angle 60 inch cable using PE-SR405FLJ coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack SMA to MCX cable assembly has a female to plug gender configuration with 50 ohm formable PE-SR405FLJ coax. The PE3W03859-60 SMA female to MCX plug cable assembly operates to 6 GHz. The right angle MCX interface on the PE-SR405FLJ cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female to MCX Plug Right Angle Cable 60 Inch Length Using PE-SR405FLJ Coax PE3W03859-60](#)



SMA Female to MCX Plug Right Angle Cable 60 Inch Length Using PE-SR405FLJ Coax

RF Cable Assemblies Technical Data Sheet

PE3W03859-60

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.5:1	
Velocity of Propagation		69.5		%
RF Shielding	100			dB
Group Delay		1.43 [4.69]		ns/ft [ns/m]
Capacitance		29 [95.14]		pF/ft [pF/m]
DC Resistance Inner Conductor		65.7 [215.55]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		10.2 [33.46]		Ohms/1000ft [Ohms/Km]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2.5	6		GHz
Insertion Loss (Max.)	1.05	1.43	2.03	3.31		dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.3dB of connector loss.

Mechanical Specifications

Cable Assembly

Length*	60 in [152.4 cm]
Diameter	0.25 in [6.35 mm]

Cable

Cable Type	PE-SR405FLJ
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor Material and Plating	Tinned Copper Composite Braid
Jacket Material	FEP, Black
Jacket Diameter	0.105 in [2.67 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female to MCX Plug Right Angle Cable 60 Inch Length Using PE-SR405FLJ Coax PE3W03859-60](#)



SMA Female to MCX Plug Right Angle Cable
60 Inch Length Using PE-SR405FLJ Coax

RF Cable Assemblies Technical Data Sheet

PE3W03859-60

One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	0.787 in [19.99 mm]

Connectors

Description	Connector 1	Connector 2
Type	SMA Female	MCX Plug Right Angle
Specification		MIL-C-39012
Impedance	50 Ohms	50 Ohms
Mating Cycles		500
Contact Material and Plating	Beryllium Copper, Gold over Nickel	Brass, Gold over Nickel
Contact Plating Specification		30 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Gold over Nickel	Brass, Gold over Nickel
Body Plating Specification		10 μ in minimum

Mechanical Specification Notes:

***All cable assemblies have a length tolerance of 1.5% or $\pm 3/8"$, whichever is greater.**

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female to MCX Plug Right Angle Cable 60 Inch Length Using PE-SR405FLJ Coax PE3W03859-60](#)



SMA Female to MCX Plug Right Angle Cable
60 Inch Length Using PE-SR405FLJ Coax

RF Cable Assemblies Technical Data Sheet

PE3W03859-60

How to Order

Part Number Configuration:

PE3W03859

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W03859-12 = 12 inches long cable
PE3W03859-100cm = 100 cm long cable

SMA Female to MCX Plug Right Angle Cable 60 Inch Length Using PE-SR405FLJ Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female to MCX Plug Right Angle Cable 60 Inch Length Using PE-SR405FLJ Coax PE3W03859-60](#)

URL: <https://www.pasternack.com/sma-female-mcx-plug-pe-sr405flj-cable-assembly-pe3w03859-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W03859-60 CAD Drawing

SMA Female to MCX Plug Right Angle Cable 60 Inch Length Using PE-SR405FLJ Coax

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	05/02/19	S. ELLIS

LENGTH MEASURED FROM
CONTACT TO CONTACT

— 1/4 HEX

1/4 HEX

SOLDER

LENGTH MEASURED FROM
CONTACT TO CONTACT

SOLDER

CONTACT

PE-SR405FLJ

CONTACT

MCX PLUG RA

MA FEMALE

SMA FEMALE

PASTERNACK an INFINITE[®] brand		<p>THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNACK CORPORATION. ALL RIGHTS RESERVED.</p>											
		SHEET 1 OF 1	REV A										
<p>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS</p> <p>TOLENCES:</p> <table style="margin-left: 20px;"> <tr> <td>$X \pm 2$</td> <td>$[0.08]$</td> <td>FRACTIONS</td> </tr> <tr> <td>$XX \pm .01$</td> <td>$[.25]$</td> <td>$\pm 1/32$</td> </tr> <tr> <td colspan="2">$XXX \pm .005$</td> <td>$[.13]$</td> <td>ANGLES $\pm 1^\circ$</td> </tr> </table> <p>ALL DIMENSIONS SHOWN ARE FOR INFORMATION ONLY.</p> <p>THIRD-ANGLE PROJECTION</p>		$X \pm 2$	$[0.08]$	FRACTIONS	$XX \pm .01$	$[.25]$	$\pm 1/32$	$XXX \pm .005$		$[.13]$	ANGLES $\pm 1^\circ$	<p>Pasterнак Enterprises, Inc. P.O. Box 16795, Irvine, CA 92623. Phone: 1.949.261.9120 1.866.727.8376 Fax: 1.949.261.7451</p> <p>www.pasterнак.com e-mail: sales@pasterнак.com</p>	
$X \pm 2$	$[0.08]$	FRACTIONS											
$XX \pm .01$	$[.25]$	$\pm 1/32$											
$XXX \pm .005$		$[.13]$	ANGLES $\pm 1^\circ$										
SIZE	CAGE	DRAWN BY	PART NUMBER										
A	53919	K. DANG	PE3W03859										

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.