



TNC Male Right Angle to SMA Male Right Angle Low Loss Cable Using LMR-200 Coax with HeatShrink and 180 Deg. Clock

RF Cable Assemblies Technical Data Sheet

PE3W06125/SP

Configuration

- Connector 1: TNC Male Right Angle
- Connector 2: SMA Male Right Angle
- Cable Type: LMR-200

Features

- Max Frequency 5.8 GHz
- Shielding Effectivity > 90 dB
- 83% Phase Velocity
- Double Shielded
- PE Jacket


Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W06125/SP TNC male right angle to SMA male right angle cable using LMR-200 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TNC to SMA cable assembly has a male to male gender configuration with 50 ohm flexible LMR-200 coax. The PE3W06125/SP TNC male to SMA male cable assembly operates to 5.8 GHz. The right angle TNC and right angle SMA interfaces on the LMR-200 cable allow for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male Right Angle to SMA Male Right Angle Low Loss Cable Using LMR-200 Coax with HeatShrink and 180 Deg. Clock PE3W06125/SP](#)



TNC Male Right Angle to SMA Male Right Angle Low Loss Cable Using LMR-200 Coax with HeatShrink and 180 Deg. Clock

RF Cable Assemblies Technical Data Sheet

PE3W06125/SP

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.4:1	
Velocity of Propagation		83		%
RF Shielding	90			dB
Group Delay		1.22 [4]		ns/ft [ns/m]
Capacitance		24.5 [80.38]		pF/ft [pF/m]
Inductance		0.061 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		5.36 [17.59]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		4.9 [16.08]		Ω/1000ft [Ω/Km]
Jacket Spark			3,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	5.8	GHz
Insertion Loss (Typ.)	0.05	0.07	0.104	0.169	0.264	dB/ft
	0.16	0.23	0.34	0.55	0.87	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2 dB for the right angle connector.

Mechanical Specifications

Cable Assembly

Weight 0.11 lbs [49.9 g]

Cable

Cable Type	LMR-200
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.195 in [4.95 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male Right Angle to SMA Male Right Angle Low Loss Cable Using LMR-200 Coax with HeatShrink and 180 Deg. Clock PE3W06125/SP](#)



TNC Male Right Angle to SMA Male Right Angle Low Loss Cable Using LMR-200 Coax with HeatShrink and 180 Deg. Clock

RF Cable Assemblies Technical Data Sheet

PE3W06125/SP

One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	2 in [50.8 mm]
Bending Moment	0.2 lbs-ft [0.27 N-m]
Flat Plate Crush	15 lbs/in [0.27 Kg/mm]
Tensile Strength	40 lbs [18.14 Kg]

Connectors

Description	Connector 1	Connector 2
Type	TNC Male Right Angle	SMA Male Right Angle
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 µin minimum	
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Gold
Body Plating Specification	100 µin minimum	
Coupling Nut Material and Plating	Brass, Nickel	Brass, Gold

Environmental Specifications

Temperature

Operating Range	-40 to +85 deg C
-----------------	------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male Right Angle to SMA Male Right Angle Low Loss Cable Using LMR-200 Coax with HeatShrink and 180 Deg. Clock PE3W06125/SP](#)



TNC Male Right Angle to SMA Male Right Angle Low Loss Cable Using LMR-200 Coax with HeatShrink and 180 Deg. Clock

RF Cable Assemblies Technical Data Sheet

PE3W06125/SP

How to Order

Part Number Configuration:

PE3W06125/SP

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W06125/SP-12 = 12 inches long cable
PE3W06125/SP-100cm = 100 cm long cable

TNC Male Right Angle to SMA Male Right Angle Low Loss Cable Using LMR-200 Coax with HeatShrink and 180 Deg. Clock from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male Right Angle to SMA Male Right Angle Low Loss Cable Using LMR-200 Coax with HeatShrink and 180 Deg. Clock PE3W06125/SP](https://www.pasternack.com/tnc-male-right-angle-to-sma-male-right-angle-low-loss-cable-using-lmr-200-coax-with-heatshrink-and-180-deg-clock-pe3w06125-sp)

URL: <https://www.pasternack.com/tnc-male-right-angle-to-sma-male-low-loss-cable-using-lmr-200-with-heatshrink-and-180-deg.-clock-pe3w06125-sp-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W06125/SP CAD Drawing

TNC Male Right Angle to SMA Male Right Angle Low Loss Cable
Using LMR-200 Coax with HeatShrink and 180 Deg. Clock



NOTES:

- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
 - CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY
- THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
PE PASTERNAK[®] an INFINITO brand		SCALE	NONE
Website: www.Pasternack.com Phone: 1.866.727.8376 1.949.261.1920		SHEET	1 OF 1
DESCRIPTION		ITEM NO.	REV
SMA Male Right Angle to TNC Male Right Angle Low Loss Cable Using LMR-200 Coax with HeatShrink and 180 Deg. Clock		PE3W06125/SP	A
SIZE	CAGE CODE	DRAWN BY	
A	53919	BPUCHASKI	
TOLERANCES:			
X = ±.2 [.5] FRACTIONS			
.XX = ±.02 [.5] ANGLES ± 1°			
XXX = ±.005 [.13]			
CABLE LENGTH TOLERANCES:			
≤12 [305] = +1 [25] / -0			
>12 [305] ≤ 60 [1524] = +2 [51] / -0			
>60 [1524] ≤ 120 [3048] = +4 [102] / -0			
>120 [3048] ≤ 300 [7620] = +6 [152] / -0			
>300 [7620] = +5% / -0			
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.			