

SMA Female to SMA Male Right Angle Cable 48 Inch Length Using RG316-DS Coax with HeatShrink



RF Cable Assemblies Technical Data Sheet


PE3W07377/HS-48

Configuration

- Connector 1: SMA Female
- Connector 2: SMA Male Right Angle
- Cable Type: RG316-DS

Features

- Max Frequency 3 GHz
- 70% Phase Velocity
- Double Shielded
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W07377/HS-48 SMA female to SMA male right angle 48 inch cable using RG316-DS coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to SMA cable assembly has a female to male gender configuration with 50 ohm flexible RG316-DS coax. The PE3W07377/HS-48 SMA female to SMA male cable assembly operates to 3 GHz. The right angle SMA interface on the RG316-DS cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.5:1	
Velocity of Propagation		70		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female to SMA Male Right Angle Cable 48 Inch Length Using RG316-DS Coax with HeatShrink PE3W07377/HS-48](#)



SMA Female to SMA Male Right Angle Cable 48 Inch Length Using RG316-DS Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE3W07377/HS-48

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Max.)	0.7	0.84	1.35	1.9	2.17	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax use in this assembly. The Insertion Loss includes an estimated insertion loss of 0.3dB of connector Loss

Mechanical Specifications

Cable Assembly

Length*

48 in [121.92 cm]

Cable

Cable Type

RG316-DS

Impedance

50 Ohms

Inner Conductor Type

Stranded

Inner Conductor Material and Plating

Copper Clad Steel, Silver

Dielectric Type

PTFE

Number of Shields

2

Shield Layer 1

Silver Plated Copper Braid

Shield Layer 2

Silver Plated Copper Braid

Jacket Material

FEP, Tan

Jacket Diameter

0.114 in [2.9 mm]

Repeated Minimum Bend Radius

0.6 in [15.24 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female to SMA Male Right Angle Cable 48 Inch Length Using RG316-DS Coax with HeatShrink PE3W07377/HS-48](#)



SMA Female to SMA Male Right Angle Cable 48 Inch Length Using RG316-DS Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE3W07377/HS-48

Connectors

Description	Connector 1	Connector 2
Type	SMA Female	SMA Male Right Angle
Specification		MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Contact Material and Plating		Brass, Gold
Contact Plating Specification		50 μ in minimum
Dielectric Type		PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification		100 μ in minimum
Coupling Nut Material and Plating		Brass, Nickel
Coupling Nut Plating Specification		100 μ in minimum
Hex Size		5/16 inch
Torque		3 in-lbs [0.34 Nm]

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or $\pm 3/8$ ", whichever is greater.

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female to SMA Male Right Angle Cable 48 Inch Length Using RG316-DS Coax with HeatShrink PE3W07377/HS-48](#)




SMA Female to SMA Male Right Angle Cable 48 Inch Length Using RG316-DS Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE3W07377/HS-48

How to Order

Part Number Configuration:



Example: PE3W07377/HS-12 = 12 inches long cable
PE3W07377/HS-100cm = 100 cm long cable

SMA Female to SMA Male Right Angle Cable 48 Inch Length Using RG316-DS Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female to SMA Male Right Angle Cable 48 Inch Length Using RG316-DS Coax with HeatShrink PE3W07377/HS-48](https://www.pasternack.com/sma-female-sma-male-rg316-ds-cable-assembly-pe3w07377-hs-48-p.aspx)

URL: <https://www.pasternack.com/sma-female-sma-male-rg316-ds-cable-assembly-pe3w07377-hs-48-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W07377/HS-48 CAD Drawing
 SMA Female to SMA Male Right Angle Cable 48 Inch
 Length Using RG316-DS Coax with HeatShrink

