



## RF Cable Assemblies Technical Data Sheet

PE3W07532-24


# Configuration

Connector 1: Snap-OnMMBX PlugConnector 2: SSMB Jack Bulkhead

Cable Type: RG316

#### **Features**

- Max Frequency 3 GHz
- 69% Phase Velocity
- FEP Jacket



## **Applications**

· General Purpose

Laboratory Use

#### Description

Pasternack's PE3W07532-24 MMBX plug snap-on to SSMB jack bulkhead 24 inch cable using RG316 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack MMBX to SSMB cable assembly has a plug to jack gender configuration with 50 ohm flexible RG316 coax. The PE3W07532-24 MMBX plug to SSMB jack cable assembly operates to 3 GHz. Our RF cable assembly with SSMB bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.5:1	
Velocity of Propagation		69		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]
Jacket Spark			2,000	Vrms

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Snap-On MMBX Plug to SSMB Jack Bulkhead Cable 24 Inch Length Using RG316 Coax PE3W07532-24

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





# RF Cable Assemblies Technical Data Sheet

PE3W07532-24

#### **Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	3	GHz
Insertion Loss (Max.)	0.52	0.68	0.96	1.26	1.36	dB

**Electrical Specification Notes:** 

The Insertion Loss data above is based on the performance specifications of the coax use in this assembly. The Insertion Loss includes an estimated insertion loss of 0.2dB of connector Loss

#### **Mechanical Specifications**

**Cable Assembly** 

Length\* 24 in [609.6 mm]
Diameter 0.188 in [4.78 mm]

Cable

Cable Type Impedance

Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields

Shield Layer 1
Jacket Material

Jacket Diameter

50 Ohms Stranded

**RG316** 

Copper Clad Steel, Silver

PTFE 1

Silver Plated Copper Braid

FEP, Tan

0.102 in [2.59 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Snap-On MMBX Plug to SSMB Jack Bulkhead Cable 24 Inch Length Using RG316 Coax PE3W07532-24

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





# RF Cable Assemblies Technical Data Sheet

PE3W07532-24

### Connectors

Description	Connector 1	Connector 2 SSMB Jack Bulkhead	
Туре	MMBX Plug		
Specification		MIL-STD-348	
Impedance	50 Ohms	50 Ohms	
Connection Method	Snap-On		
Mating Cycles	100		
Contact Material and Plating	Beryllium Copper, Gold	Gold	
Contact Plating Specification		MIL-G-45204	
Dielectric Type	PTFE	PTFE	
Outer Conductor Material and Plating	Brass, Gold		
Body Material and Plating	Brass, Gold	s, Gold Brass, Gold	
Body Plating Specification	A	MIL-G-45204	

Mechanical Specification Notes:

Compliance Certifications (see product page for current document)

### **Plotted and Other Data**

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Snap-On MMBX Plug to SSMB Jack Bulkhead Cable 24 Inch Length Using RG316 Coax PE3W07532-24

<sup>\*</sup>All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.





### RF Cable Assemblies Technical Data Sheet

PE3W07532-24

#### **How to Order**



Example: PE3W07532-12 = 12 inches long cable

PE3W07532-100cm = 100 cm long cable

Snap-On MMBX Plug to SSMB Jack Bulkhead Cable 24 Inch Length Using RG316 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Snap-On MMBX Plug to SSMB Jack Bulkhead Cable 24 Inch Length Using RG316 Coax PE3W07532-24

URL: https://www.pasternack.com/mmbx-plug-ssmb-jack-rg316u-cable-assembly-pe3w07532-24-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE3W07532-24 CAD Drawing
Snap-On MMBX Plug to SSMB Jack Bulkhead Cable 24 Inch Length Using RG316 Coax

