

TNC Female Bulkhead to MCX Plug Right Angle Cable Using RG174 Coax with 90 Deg. Clock





PE3W07886/SP

Configuration

- Connector 1: TNC Female Bulkhead
- Connector 2: MCX Plug Right Angle
- Cable Type: RG174
- Coax Flex Type: Flexible

Features

- Max Frequency 1 GHz
- 66% Phase Velocity
- PVC Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W07886/SP TNC female bulkhead to MCX plug right angle cable using RG174 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TNC to MCX cable assembly has a female to plug gender configuration with 50 ohm flexible RG174 coax. The PE3W07886/SP TNC female to MCX plug cable assembly operates to 1 GHz. The right angle MCX interface on the RG174 cable allows for easier connections in tight spaces. Our RF cable assembly with TNC bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Velocity of Propagation	66			%
Capacitance	31.08 [101.97]			pF/ft [pF/m]

Specifications by Frequency

TNC Female Bulkhead to MCX Plug Right Angle Cable Using RG174 Coax with 90 Deg. Clock



PE3W07886/SP

Part Number	Length	Description	F1	F2	F3	F4	Units	Weight (lbs)
		Frequency	100	250	500	1000	MHz	
PE3W07886/SP	Custom Lengths Available	Insertion Loss (Typ.)	0.08	0.14	0.21	0.32	dB/ft	
			0.28	0.45	0.7	1.05	dB/m	
PE3W07886/SP-12	12 inch	Insertion Loss (Typ.)	0.39	0.44	0.52	0.62	dB	0.065
PE3W07886/SP-24	24 inch	Insertion Loss (Typ.)	0.47	0.58	0.73	0.94	dB	0.074
PE3W07886/SP-36	36 inch	Insertion Loss (Typ.)	0.56	0.72	0.94	1.26	dB	0.083
PE3W07886/SP-48	48 inch	Insertion Loss (Typ.)	0.64	0.85	1.15	1.58	dB	0.092
PE3W07886/SP-72	72 inch	Insertion Loss (Typ.)	0.81	1.13	1.57	2.22	dB	0.11

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB
 Loss due to Connector 2: 0.2 dB
 Base Weight: 0.065 pounds
 Additional Weight per Inch: 0.00075 pounds

Mechanical Specifications

Cable Assembly

Weight 0.065 lbs [29.48 g]

Cable

Cable Type RG174
 Impedance 50 Ohms
 Inner Conductor Type Stranded
 Inner Conductor Material and Plating Copper Clad Steel
 Dielectric Type PE
 Number of Shields 1
 Shield Layer 1 Tinned Copper Braid
 Jacket Material PVC, Black
 Jacket Diameter 0.11 in [2.79 mm]

Connectors

Description	Connector 1	Connector 2
Type	TNC Female Bulkhead	MCX Plug Right Angle
Specification	MIL-STD-348	CECC 22220
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Contact Material and Plating	Phosphor Bronze, Gold	Brass, Gold
Contact Plating Specification		30 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification		100 μ in minimum

TNC Female Bulkhead to MCX Plug Right Angle Cable Using RG174 Coax with 90 Deg. Clock



PE3W07886/SP

Environmental Specifications

Operating Range Temperature

-40 to +60 deg C

Compliance Certifications (see [product page](#) for current document)


Plotted and Other Data

Notes:

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3W07886/SP-12 = 12 inches long cable
PE3W07886/SP-100cm = 100 cm long cable

TNC Female Bulkhead to MCX Plug Right Angle Cable Using RG174 Coax with 90 Deg. Clock from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Female Bulkhead to MCX Plug Right Angle Cable Using RG174 Coax with 90 Deg. Clock PE3W07886/SP](#)

URL: <https://www.pasternack.com/tnc-female-bulkhead-to-mcx-plug-cable-using-rg174-with-90-deg.-clock-pe3w07886-sp-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W07886/SP CAD Drawing

TNC Female Bulkhead to MCX Plug Right Angle Cable Using RG174 Coax with 90 Deg. Clock

