



QMA Male Right Angle to SMA Male Low Loss Cable Using LMR-240 Coax

TECHNICAL DATA SHEET


PE3W06098

Configuration

- Connector 1: QMA Male Right Angle
- Connector 2: SMA Male
- Cable Type: LMR-240
- Coax Flex Type: Flexible

Features

- Max Frequency 5.8 GHz
- Shielding Effectivity > 90 dB
- 84% Phase Velocity
- Double Shielded
- PE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W06098 QMA male right angle to SMA male cable using LMR-240 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack QMA to SMA cable assembly has a male to male gender configuration with 50 ohm flexible LMR-240 coax. The PE3W06098 QMA male to SMA male cable assembly operates to 5.8 GHz. The right angle QMA interface on the LMR-240 cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [QMA Male Right Angle to SMA Male Low Loss Cable Using LMR-240 Coax PE3W06098](#)



QMA Male Right Angle to SMA Male Low Loss Cable Using LMR-240 Coax

TECHNICAL DATA SHEET

PE3W06098

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.4:1	
Velocity of Propagation		84		%
RF Shielding	90			dB
Group Delay		1.21 [3.97]		ns/ft [ns/m]
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		3.2 [10.5]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		3.89 [12.76]		Ω/1000ft [Ω/Km]
Jacket Spark			5,000	Vrms

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
			Frequency	250	500	1000	2500	5800	MHz
PE3W06098	Custom Lengths Available	Insertion Loss (Typ.)	0.04	0.06	0.08	0.12	0.2	dB/ft	
			0.14	0.2	0.27	0.4	0.66	dB/m	
PE3W06098-12	12 inch	Insertion Loss (Typ.)	0.39	0.41	0.43	0.47	0.55	dB	0.062
PE3W06098-24	24 inch	Insertion Loss (Typ.)	0.43	0.47	0.51	0.59	0.75	dB	0.091
PE3W06098-36	36 inch	Insertion Loss (Typ.)	0.47	0.53	0.59	0.71	0.95	dB	0.12
PE3W06098-48	48 inch	Insertion Loss (Typ.)	0.51	0.59	0.67	0.83	1.15	dB	0.15
PE3W06098-60	60 inch	Insertion Loss (Typ.)	0.55	0.65	0.75	0.95	1.35	dB	0.175

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.25 dB

Loss due to Connector 2: 0.1 dB

Base Weight: 0.062 pounds

Additional Weight per Inch: 0.00234 pounds

Mechanical Specifications

Cable Assembly

Weight 0.073 lbs [33.11 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [QMA Male Right Angle to SMA Male Low Loss Cable Using LMR-240 Coax PE3W06098](#)



QMA Male Right Angle to SMA Male Low Loss Cable Using LMR-240 Coax

TECHNICAL DATA SHEET

PE3W06098

Cable

Cable Type	LMR-240
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.24 in [6.1 mm]

One Time Minimum Bend Radius	0.75 in [19.05 mm]
Repeated Minimum Bend Radius	2.5 in [63.5 mm]
Bending Moment	0.25 lbs-ft [0.34 N-m]
Flat Plate Crush	20 lbs/in [0.36 Kg/mm]
Tensile Strength	80 lbs [36.29 Kg]

Connectors

Description	Connector 1	Connector 2
Type	QMA Male Right Angle Push-On	SMA Male Threaded
Impedance	50 Ohms	50 Ohms
Mating Cycles		500
Contact Material and Plating	Beryllium Copper, Gold	Brass, Gold
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Nickel	
Body Material and Plating	Brass, Nickel	Brass, Gold
Coupling Nut Material and Plating		Brass, Gold
Hex Size		16-May inch
Torque		3 in-lbs [0.34 Nm]

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [QMA Male Right Angle to SMA Male Low Loss Cable Using LMR-240 Coax PE3W06098](#)



QMA Male Right Angle to SMA Male Low Loss Cable Using LMR-240 Coax

TECHNICAL DATA SHEET

PE3W06098

How to Order

Part Number Configuration:

PE3W06098- **xx****uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W06098-12 = 12 inches long cable
PE3W06098-100cm = 100 cm long cable

QMA Male Right Angle to SMA Male Low Loss Cable Using LMR-240 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [QMA Male Right Angle to SMA Male Low Loss Cable Using LMR-240 Coax PE3W06098](#)

URL: <https://www.pasternack.com/qma-male-right-angle-to-sma-male-low-loss-cable-using-lmr-240-pe3w06098-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W06098 CAD Drawing

QMA Male Right Angle to SMA Male Low Loss Cable Using LMR-240 Coax

