



## MMCX Plug to N Male Right Angle Cable Using RG316 Coax with HeatShrink

### RF Cable Assemblies Technical Data Sheet



**PE3W06179/HS**

#### Configuration

- Connector 1: MMCX Plug
- Connector 2: N Male Right Angle
- Cable Type: RG316

#### Features

- Max Frequency 3 GHz
- 69% Phase Velocity
- FEP Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3W06179/HS MMCX plug to type N male right angle cable using RG316 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack MMCX to type N cable assembly has a plug to male gender configuration with 50 ohm flexible RG316 coax. The PE3W06179/HS MMCX plug to type N male cable assembly operates to 3 GHz. The right angle type N interface on the RG316 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MMCX Plug to N Male Right Angle Cable Using RG316 Coax with HeatShrink PE3W06179/HS](#)



## MMCX Plug to N Male Right Angle Cable Using RG316 Coax with HeatShrink

### RF Cable Assemblies Technical Data Sheet

**PE3W06179/HS**

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		69		%
Operating Voltage (AC)			250	Vrms
Jacket Spark			2,000	Vrms

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.11	0.16	0.238	0.38	0.58	dB/ft
	0.36	0.52	0.78	1.25	1.9	dB/m

#### Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2 dB for the right angle connector and 0.1 dB for the straight connector.

#### Mechanical Specifications

##### Cable Assembly

Weight 0.124 lbs [56.25 g]

##### Cable

Cable Type RG316  
Impedance 50 Ohms  
Inner Conductor Type Stranded  
Inner Conductor Material and Plating Copper Clad Steel, Silver  
Dielectric Type PTFE  
Number of Shields 1  
Shield Layer 1 Silver Plated Copper Braid  
Jacket Material FEP, Tan  
Jacket Diameter 0.102 in [2.59 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MMCX Plug to N Male Right Angle Cable Using RG316 Coax with HeatShrink PE3W06179/HS](#)



## MMCX Plug to N Male Right Angle Cable Using RG316 Coax with HeatShrink

### RF Cable Assemblies Technical Data Sheet

**PE3W06179/HS**

#### Connectors

Description	Connector 1	Connector 2
Type	MMCX Plug	N Male Right Angle
Specification	BS EN 122340	
Impedance	50 Ohms	50 Ohms
Mating Cycles		500
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 $\mu$ in minimum	
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Gold	
Outer Conductor Plating Specification	3 $\mu$ in minimum	
Body Material and Plating	Brass, Gold	Brass, Tri-Metal
Body Plating Specification	3 $\mu$ in minimum	
Coupling Nut Material and Plating		Brass, Tri-Metal

#### Environmental Specifications

##### Temperature

Operating Range

-55 to +155 deg C

#### Compliance Certifications (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MMCX Plug to N Male Right Angle Cable Using RG316 Coax with HeatShrink PE3W06179/HS](#)




## MMCX Plug to N Male Right Angle Cable Using RG316 Coax with HeatShrink

### RF Cable Assemblies Technical Data Sheet

**PE3W06179/HS**

#### How to Order

Part Number Configuration:



Example: PE3W06179/HS-12 = 12 inches long cable  
PE3W06179/HS-100cm = 100 cm long cable

MMCX Plug to N Male Right Angle Cable Using RG316 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MMCX Plug to N Male Right Angle Cable Using RG316 Coax with HeatShrink PE3W06179/HS](#)

URL: <https://www.pasternack.com/mmcx-plug-to-n-male-cable-using-rg316-with-heatshrink-pe3w06179-hs-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3W06179/HS CAD Drawing

MMCX Plug to N Male Right Angle Cable Using RG316 Coax with HeatShrink

