



MCX Plug Right Angle to MMCX Plug Cable Using RG316 Coax

RF Cable Assemblies Technical Data Sheet


PE3W06262

Configuration

- Connector 1: MCX Plug Right Angle
- Connector 2: MMCX Plug
- Cable Type: RG316

Features

- Max Frequency 3 GHz
- 69% Phase Velocity
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W06262 MCX plug right angle to MMCX plug cable using RG316 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack MCX to MMCX cable assembly has a plug to plug gender configuration with 50 ohm flexible RG316 coax. The PE3W06262 MCX plug to MMCX plug cable assembly operates to 3 GHz. The right angle MCX interface on the RG316 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MCX Plug Right Angle to MMCX Plug Cable Using RG316 Coax PE3W06262](#)



MCX Plug Right Angle to MMCX Plug Cable Using RG316 Coax

RF Cable Assemblies Technical Data Sheet

PE3W06262

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		69		%
Operating Voltage (AC)			250	Vrms
Jacket Spark			2,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.11	0.16	0.238	0.38	0.58	dB/ft
	0.36	0.52	0.78	1.25	1.9	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB for the MMCX plug connector and 0.2 dB for the MCX plug connector.

Mechanical Specifications

Cable Assembly

Weight 0.026 lbs [11.79 g]

Cable

Cable Type	RG316
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.102 in [2.59 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MCX Plug Right Angle to MMCX Plug Cable Using RG316 Coax PE3W06262](#)



MCX Plug Right Angle to MMCX Plug Cable Using RG316 Coax

RF Cable Assemblies Technical Data Sheet

PE3W06262

Connectors

Description	Connector 1	Connector 2
Type	MCX Plug Right Angle	MMCX Plug
Specification	CECC 22220	BS EN 122340
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 µin minimum	30 µin minimum
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating		Brass, Gold
Outer Conductor Plating Specification		3 µin minimum
Body Material and Plating	Brass, Nickel	Brass, Gold
Body Plating Specification	100 µin minimum	3 µin minimum

Environmental Specifications

Temperature

Operating Range

-40 to +60 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MCX Plug Right Angle to MMCX Plug Cable Using RG316 Coax PE3W06262](#)



MCX Plug Right Angle to MMCX Plug Cable Using RG316 Coax

RF Cable Assemblies Technical Data Sheet

PE3W06262

How to Order

Part Number Configuration:

PE3W06262

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W06262-12 = 12 inches long cable
PE3W06262-100cm = 100 cm long cable


MCX Plug Right Angle to MMCX Plug Cable Using RG316 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MCX Plug Right Angle to MMCX Plug Cable Using RG316 Coax PE3W06262](https://www.pasternack.com/mcx-plug-right-angle-to-mmcx-plug-cable-using-rg316-pe3w06262-p.aspx)

URL: <https://www.pasternack.com/mcx-plug-right-angle-to-mmcx-plug-cable-using-rg316-pe3w06262-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W06262 CAD Drawing



1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED, LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN WHOLE OR PART WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVISION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILL METERS	PE PASTERNAK® an INFINITO® brand	 	INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	SCALE: NONE SHEET: 1 OF 1	DESCRIPTION MMCX Plug Right Angle to MMCX Plug Cable Using RG316 Coax	REV: A
Website: www.Pasternack.com Phone: 1.866.727.8376 1.949.261.1920	ITEM NO.	HBAKKE	PE3W06262	SIZE: A	CAGE CODE: 53919	REV: A
TOLERANCES: X ± .02 [.5] FRACTIONS XX ± .02 [.5] 1/32 XXX ± .005 [.13] ANGLES ± 1°	CABLE LENGTH TOLERANCES: >12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	DRAWN BY	ITEM NO.	SIZE: A	CAGE CODE: 53919	REV: A
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.	HBAKKE	ITEM NO.	PE3W06262	SIZE: A	CAGE CODE: 53919	REV: A