

## Waterproof IP68 N Male (Plug) Right Angle to N Male (Plug) Low Loss Cable Using LMR-400 Coax with Times Microwave Components




### PE3W06371/WP

#### Configuration

- Connector 1: N Male Right Angle
- Connector 2: N Male
- Cable Type: LMR-400
- Coax Flex Type: Flexible

#### Features

- Max Frequency 6 GHz
- Shielding Effectivity > 90 dB
- 85% Phase Velocity
- Double Shielded
- PE Jacket
- Silicone Connector Boot
- IP68 Rated



#### Applications

- General Purpose
- Laboratory Use

#### Description

The Pasternack PE3W06371/WP is a weatherproof low loss cable assembly that comes with type N male connection with weatherproof boot on one end and type N male on the other. Pasternack's RF coaxial cable assembly products are designed for typical use, production, laboratory test and measurement, defense/military, aerial antenna towers, etc. The low loss cable has a 50 Ohm impedance and is specifically ready for quicker shipment than most in the industry can provide.

This weatherproof low loss RF cable assembly operates at a maximum frequency of 6 GHz. Our RF cable assembly has a PE jacket with 0.405 inches diameter. The type N male to type N male cable assembly PE3W06371/WP is built with LMR-400 coax, which has a flexible design. This RF cable assembly with 0.5 inches diameter has copper clad aluminum as cable's inner conducting material and PE (F) dielectric type. The weatherproof boot low loss cable can operate at a temperature range of -40 to 85 degrees C. Additional dimensions, specifications, and CAD drawings for this PE3W06371/WP low loss RF cable are available on our downloadable PDF datasheet.

Pasternack stocks a wide selection of weatherproof low loss cable assemblies that ship the same business day as ordered from our warehouse. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal type N male to type N male cable assembly as per your requirements.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		85		%
RF Shielding	90			dB
Capacitance		23.9 [78.41]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]

Waterproof IP68 N Male (Plug) Right Angle to N Male (Plug) Low Loss Cable Using LMR-400 Coax with Times Microwave Components



## PE3W06371/WP

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
DC Resistance Inner Conductor		1.39 [4.56]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		1.65 [5.41]		Ohms/1000ft [Ohms/Km]
Dielectric Withstanding Voltage (DC)			2,500	Vdc
Jacket Spark			8,000	Vrms

### Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
			Frequency					MHz	
PE3W06371/WP	Custom Lengths Available	Insertion Loss (Typ.)	0.02	0.028	0.041	0.068	0.108	dB/ft	
			0.07	0.1	0.14	0.23	0.36	dB/m	
PE3W06371/WP-24	24 In	Insertion Loss (Typ.)	0.34	0.36	0.39	0.44	0.52	dB	0.871
PE3W06371/WP-36	36 In	Insertion Loss (Typ.)	0.36	0.39	0.43	0.51	0.63	dB	0.938
PE3W06371/WP-48	48 In	Insertion Loss (Typ.)	0.38	0.42	0.47	0.58	0.74	dB	1.005
PE3W06371/WP-60	60 In	Insertion Loss (Typ.)	0.4	0.44	0.51	0.64	0.84	dB	1.072

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.2 dB
Loss due to Connector 2:	0.1 dB
Base Weight:	0.804 pounds
Additional Weight per Inch:	0.00558 pounds

### Mechanical Specifications

#### Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.804 lbs [364.69 g]

#### Cable

Cable Type	LMR-400
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Aluminum
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE
Jacket Diameter	0.405 in [10.29 mm]
One Time Minimum Bend Radius	1 in [25.4 mm]
Repeated Minimum Bend Radius	4 in [101.6 mm]
Bending Moment	0.5 lbs-ft [0.68 N-m]
Flat Plate Crush	40 lbs/in [0.71 Kg/mm]
Tensile Strength	160 lbs [72.57 Kg]

Waterproof IP68 N Male (Plug) Right Angle to N Male (Plug) Low Loss Cable Using LMR-400 Coax with Times Microwave Components



## PE3W06371/WP

### Connectors

Description	Connector 1	Connector 2
Type	N Male Right Angle	N Male
Option		Weatherproof Boot
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification		50 µin minimum
Dielectric Type	Teflon	PTFE
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification		150 µin minimum
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Plating Specification		150 µin minimum
Boot Material	Silicone	Silicone

### Environmental Specifications

Operating Range Temperature	-40 to +85 deg C
Ingress Protection (IP) Rating	IP68

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:  
Values at 25°C, sea level.

Waterproof IP68 N Male (Plug) Right Angle to N Male (Plug) Low Loss Cable Using LMR-400 Coax with Times Microwave Components




**PE3W06371/WP**

**Typical Performance Data**

**How to Order**

Part Number Configuration:

**PE3W06371/WP - xx uu**



Example: PE3W06371/WP-12 = 12 inches long cable  
PE3W06371/WP-100cm = 100 cm long cable

Waterproof IP68 N Male (Plug) Right Angle to N Male (Plug) Low Loss Cable Using LMR-400 Coax with Times Microwave Components from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Waterproof IP68 N Male \(Plug\) Right Angle to N Male \(Plug\) Low Loss Cable Using LMR<sup>®</sup>-400 Coax with Times Microwave Components PE3W06371/WP](https://www.pasternack.com/waterproof-ip68-n-male-plug-right-angle-to-n-male-plug-low-loss-cable-using-lmr-400-pe3w06371-wp-p.aspx)

URL: <https://www.pasternack.com/waterproof-ip68-n-male-plug-right-angle-to-n-male-plug-low-loss-cable-using-lmr-400-pe3w06371-wp-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE3W06371/WP CAD Drawing

Waterproof IP68 N Male (Plug) Right Angle to N Male (Plug) Low Loss Cable  
Using LMR-400 Coax with Times Microwave Components



**NOTES:**

1. CABLE ASSEMBLY LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE IN INCHES. DIMENSIONS IN [ ] ARE MILLIMETERS.

TOLERANCES:

.X = +.2 [-.5]	FRACTIONS
.XX = ±.02 [0.5]	± 1/32
.XXX = ±.005 [0.13]	ANGLES ± 1°

CABLE LENGTH TOLERANCES:

>12 [305]	±.60 [15.24]
>60 [1524]	±.120 [3.048]
>120 [3048]	±.300 [7.620]

ALL DIMENSIONS ARE FOR REFERENCE ONLY. UNDIMENSIONED NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.

<b>PE PASTERNAK</b> an INFINITE brand		
Website: <a href="http://www.Pasternack.com">www.Pasternack.com</a> Phone: 1.866.727.8376   1.949.261.1920		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE: NONE SHEET: 1 OF 1
DESCRIPTION <b>WEATHERPROOF BOOT N MALE RIGHT ANGLE TO N MALE LOW LOSS CABLE USING LMR-400 COAX WITH TIMES MICROWAVE COMPONENTS</b>		
SIZE	CAGE CODE	ITEM NO.
A	53919	PE3W06371/WP
REV	DRAWN BY	REV
A	DMAY	A