

NEX10 Male Right Angle to NEX10 Male Right Angle Low PIM Cable Using TFT-5G-402 Coax with HeatShrink and 225 Deg. Clock


PE3W08440/HS/PH225

Configuration

- Connector 1: NEX10 Male Right Angle
- Connector 2: NEX10 Male Right Angle
- Cable Type: TFT-5G-402
- Coax Flex Type: Flexible

Features

- Max Frequency 4 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > 80 dB
- 76% Phase Velocity
- Double Shielded
- FEP Jacket
- 500 Mating Cycles



Applications

- General Purpose
- Laboratory Use
- Low PIM Applications

Description

Pasternack's PE3W08440/HS/PH225 NEX10 male right angle to NEX10 male right angle cable using TFT-5G-402 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack NEX10 to NEX10 cable assembly has a male to male gender configuration with 50 ohm flexible TFT-5G-402 coax. The PE3W08440/HS/PH225 NEX10 male to NEX10 male cable assembly operates to 4 GHz. Our low PIM design also offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The right angle NEX10 interfaces on the TFT-5G-402 cable allow for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 80 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
VSWR			1.4:1	
Velocity of Propagation		76		%
RF Shielding	80			dB
Passive Intermodulation			-160	dBc

NEX10 Male Right Angle to NEX10 Male Right Angle Low PIM Cable Using TFT-5G-402 Coax with HeatShrink and 225 Deg. Clock

PE3W08440/HS/PH225

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Capacitance		26.7 [87.6]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	4	GHz
Insertion Loss (Max.)	1.017555	1.043887	1.081931	1.111241	1.239528	dB/ft
	3.34	3.42	3.55	3.65	4.07	dB/m

Mechanical Specifications

Cable Assembly

Width/Diameter	0.472 in [11.99 mm]
Weight	0.06 lbs [27.22 g]

Cable

Cable Type	TFT-5G-402
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PTFE
Number of Shields	2
Shield Layer 1	Tin
Outer Conductor 1 Material and Plating	Copper, Tin
Jacket Material	FEP, Blue
Jacket Diameter	0.16 in [4.06 mm]
One Time Minimum Bend Radius	0.75 in [19.05 mm]

NEX10 Male Right Angle to NEX10 Male
Right Angle Low PIM Cable Using TFT-5G-402 Coax
with HeatShrink and 225 Deg. Clock

PE3W08440/HS/PH225**Connectors**

Description	Connector 1	Connector 2
Type	NEX10 Male Right Angle	NEX10 Male Right Angle
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Right Angle
Mating Cycles	500	500
Contact Material and Plating	Brass, Silver	Brass, Silver
Contact Plating Specification	200 µin	200 µin
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification	100 µin	100 µin
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Plating Specification	100 µin	100 µin
Torque	13 in-lbs 1.47 Nm	13 in-lbs 1.47 Nm

Environmental Specifications

Operating Range Temperature -40 to +125 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

NEX10 Male Right Angle to NEX10 Male
Right Angle Low PIM Cable Using TFT-5G-402 Coax
with HeatShrink and 225 Deg. Clock

PE3W08440/HS/PH225

Typical Performance Data

How to Order

Part Number Configuration: **PE3W08440/HS/PH225** **- xx** **uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: PE3W08440/HS/PH225-12 = 12 inches long cable
PE3W08440/HS/PH225-100cm = 100 cm long cable

NEX10 Male Right Angle to NEX10 Male Right Angle Low PIM Cable Using TFT-5G-402 Coax with HeatShrink and 225 Deg. Clock from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [NEX10 Male Right Angle to NEX10 Male Right Angle Low PIM Cable Using TFT-5G-402 Coax with HeatShrink and 225 Deg. Clock PE3W08440/HS/PH225](#)

URL: <https://www.pasternack.com/nex10-male-right-angle-to-nex10-male-low-pim-cable-using-tft-5g-402-with-heatshrink-and-225-deg.-clock-pe3w08440-hs-ph225-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.