

SMA Male to SSMB Plug Cable Using RG316 Coax with HeatShrink





PE3W07141/HS

Configuration

- Connector 1: SMA Male
- Connector 2: SSMB Plug
- Cable Type: RG316
- Coax Flex Type: Flexible

Features

- Max Frequency 3 GHz
- 69% Phase Velocity
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W07141/HS SMA male to SSMB plug cable using RG316 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to SSMB cable assembly has a male to plug gender configuration with 50 ohm flexible RG316 coax. The PE3W07141/HS SMA male to SSMB plug cable assembly operates to 3 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		69		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]
Operating Voltage (AC)			250	Vrms
Jacket Spark			2,000	Vrms

Specifications by Frequency

SMA Male to SSMB Plug Cable Using RG316 Coax with HeatShrink



PE3W07141/HS

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	100	250	500	1000	3000	MHz	
PE3W07141/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.11	0.16	0.238	0.38	0.58	dB/ft	
			0.37	0.53	0.79	1.25	1.91	dB/m	
PE3W07141/HS-12	12 Inch	Insertion Loss (Typ.)	0.46	0.51	0.59	0.73	0.93	dB	0.028
PE3W07141/HS-24	24 Inch	Insertion Loss (Typ.)	0.57	0.67	0.83	1.11	1.51	dB	0.038
PE3W07141/HS-36	36 Inch	Insertion Loss (Typ.)	0.68	0.83	1.07	1.49	2.09	dB	0.048
PE3W07141/HS-48	48 Inch	Insertion Loss (Typ.)	0.79	0.99	1.31	1.87	2.67	dB	0.058
PE3W07141/HS-72	72 Inch	Insertion Loss (Typ.)	1.01	1.31	1.78	2.63	3.83	dB	0.078

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.25 dB
Loss due to Connector 2: 0.1 dB
Base Weight: 0.028 pounds
Additional Weight per Inch: 0.32917 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter 0.5 in [12.7 mm]
Weight 0.028 lbs [12.7 g]

Cable

Cable Type	RG316
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.102 in [2.59 mm]

SMA Male to SSMB Plug Cable Using RG316 Coax with HeatShrink



PE3W07141/HS

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SSMB Plug
Specification		MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold
Contact Plating Specification	15 μ in minimum	30 μ in minimum
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating		Beryllium Copper, Gold
Outer Conductor Plating Specification		30 μ in minimum
Body Material and Plating	Brass, Nickel	Brass, Gold
Body Plating Specification	200 μ in minimum	30 μ in minimum
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	200 μ in minimum	

Environmental Specifications

Operating Range Temperature -40 to +125 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

SMA Male to SSMB Plug Cable Using RG316 Coax with HeatShrink



PE3W07141/HS

Typical Performance Data

How to Order

Part Number Configuration:

PE3W07141/HS - xx uu

Legend:

- Unit of Measure:
cm = Centimeters
<blank> = Inches
- Length
- Base Number

Example: PE3W07141/HS-12 = 12 inches long cable
PE3W07141/HS-100cm = 100 cm long cable

SMA Male to SSMB Plug Cable Using RG316 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SSMB Plug Cable Using RG316 Coax with HeatShrink PE3W07141/HS](#)

URL: <https://www.pasternack.com/sma-male-to-ssmb-plug-cable-using-rg316-with-heatshrink-pe3w07141-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W07141/HS CAD Drawing

SMA Male to SSMB Plug Cable Using RG316 Coax with HeatShrink



NOTES:

36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED.
LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6
INCHES FROM EACH CONNECTOR.

2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND
DESCRIPTION

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE, WHERE EXPORTED FROM THE UNITED STATES, IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

HEATSHRINK					ITEM NO.	REV
E	CAGE CODE	DRAWN BY	HBAKKE	PE3W07141/HS	A	
	53919					

© 2023 Infinite Electronics, Inc. Pasternack is a registered trademark of Infinite Electronics, Inc.

+1 (866) 558-2786 | sales@pasternack.com | pasternack.com