

N Male to TNC Female Bulkhead Cable
48 Inch Length Using RG400 Coax



RF Cable Assemblies Technical Data Sheet

PE3W07264-48

Configuration

- Connector 1: N Male
- Connector 2: TNC Female Bulkhead
- Cable Type: RG400

Features

- Max Frequency 6 GHz
- 70% Phase Velocity
- Double Shielded
- FEP Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W07264-48 type N male to TNC female bulkhead 48 inch cable using RG400 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to TNC cable assembly has a male to female gender configuration with 50 ohm flexible RG400 coax. The PE3W07264-48 type N male to TNC female cable assembly operates to 6 GHz. Our RF cable assembly with TNC bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to TNC Female Bulkhead Cable 48 Inch Length Using RG400 Coax PE3W07264-48](#)

**N Male to TNC Female Bulkhead Cable
48 Inch Length Using RG400 Coax**

RF Cable Assemblies Technical Data Sheet
PE3W07264-48
Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.45:1	
Velocity of Propagation		70		%
Capacitance		32 [104.99]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	6	GHz
Insertion Loss (Max.)	0.4	0.44	0.8	0.84	1.52	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax used in this assembly. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications
Cable Assembly

Length*	48 in [121.92 cm]
Diameter	0.812 in [20.62 mm]

Cable

Cable Type	RG400
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.195 in [4.95 mm]

Repeated Minimum Bend Radius

1 in [25.4 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to TNC Female Bulkhead Cable 48 Inch Length Using RG400 Coax PE3W07264-48](#)

**N Male to TNC Female Bulkhead Cable
48 Inch Length Using RG400 Coax**

RF Cable Assemblies Technical Data Sheet
PE3W07264-48
Connectors

Description	Connector 1	Connector 2
Type	N Male	TNC Female Bulkhead
Specification	MIL-STD-348	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Silver	Brass, Gold
Contact Plating Specification	ASTM-B700	30 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	ASTM-B689	100 μ in minimum
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	ASTM-B689	

Environmental Specifications
Temperature

Operating Range

-55 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

 Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to TNC Female Bulkhead Cable 48 Inch Length Using RG400 Coax PE3W07264-48](#)

N Male to TNC Female Bulkhead Cable
48 Inch Length Using RG400 Coax



RF Cable Assemblies Technical Data Sheet

PE3W07264-48

How to Order

Part Number Configuration:

PE3W07264

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W07264-12 = 12 inches long cable
PE3W07264-100cm = 100 cm long cable

N Male to TNC Female Bulkhead Cable 48 Inch Length Using RG400 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to TNC Female Bulkhead Cable 48 Inch Length Using RG400 Coax PE3W07264-48](#)



URL:

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W07264-48 CAD Drawing

N Male to TNC Female Bulkhead Cable 48 Inch Length Using RG400 Coax

REVISIONS				
REV.	DESCRIPTION	DATE	APPROVED	
A	INITIAL RELEASE	8/20/2020	S.SELLS	



<p>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS TOLERANCES:</p> <table border="0"> <tr> <td>$X = \pm 2$</td><td>$[5.08]$</td><td>FRACTIONS</td></tr> <tr> <td>$XX = \pm .02$</td><td>$[.51]$</td><td>$\pm 1/32$</td></tr> <tr> <td>$XXX = \pm .005$</td><td>$[.13]$</td><td>ANGLES $\pm 1^\circ$</td></tr> </table> <p>CABLE LENGTH (L) TOLERANCES:</p> <table border="0"> <tr> <td>$L \leq 12$</td><td>$[305]$</td><td>$= +1 [25] / -0$</td></tr> <tr> <td>$12 [305] < L \leq 60 [1524]$</td><td>$= +2 [51] / -0$</td></tr> <tr> <td>$60 [1524] < L \leq 120 [3048]$</td><td>$= +4 [102] / -0$</td></tr> <tr> <td>$120 [3048] < L \leq 300 [7620]$</td><td>$= +6 [152] / -0$</td></tr> <tr> <td>$300 [7620] < L$</td><td>$= +5\% L / -0$</td></tr> </table> <p>ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.</p>	$X = \pm 2$	$[5.08]$	FRACTIONS	$XX = \pm .02$	$[.51]$	$\pm 1/32$	$XXX = \pm .005$	$[.13]$	ANGLES $\pm 1^\circ$	$L \leq 12$	$[305]$	$= +1 [25] / -0$	$12 [305] < L \leq 60 [1524]$	$= +2 [51] / -0$	$60 [1524] < L \leq 120 [3048]$	$= +4 [102] / -0$	$120 [3048] < L \leq 300 [7620]$	$= +6 [152] / -0$	$300 [7620] < L$	$= +5\% L / -0$	<p>THIRD ANGLE PROJECTION</p> <p>THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNACK CORPORATION ALL RIGHTS RESERVED.</p> <p>PASTERNACK® an INFINITE® brand</p> <p>Pasterнак Enterprises, Inc. P.O. Box 16759, Irvine, CA 92623. Phone: 1.949.261.1920 1.866.727.8376 Fax: 1.949.261.7451 Website: www.pasterнак.com E-mail: sales@pasterнак.com</p> <p>SHEET 1 OF 1</p> <p>SCALE N/A</p> <p>ITEM NO. PE3W07264</p> <p>REV A</p>
$X = \pm 2$	$[5.08]$	FRACTIONS																			
$XX = \pm .02$	$[.51]$	$\pm 1/32$																			
$XXX = \pm .005$	$[.13]$	ANGLES $\pm 1^\circ$																			
$L \leq 12$	$[305]$	$= +1 [25] / -0$																			
$12 [305] < L \leq 60 [1524]$	$= +2 [51] / -0$																				
$60 [1524] < L \leq 120 [3048]$	$= +4 [102] / -0$																				
$120 [3048] < L \leq 300 [7620]$	$= +6 [152] / -0$																				
$300 [7620] < L$	$= +5\% L / -0$																				

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE
WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.