

## SMP Female to SMP Female Cable Using Tinned RG405 Coax , LF Solder



### RF Cable Assemblies Technical Data Sheet

**PE3W08858LF**

#### Configuration

- Connector 1: SMP Female
- Connector 2: SMP Female
- Cable Type: RG405 Tinned

#### Features

- Max Frequency 18 GHz

#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3W08858LF SMP female to SMP female cable using tinned RG405 coax is part of our full line of RF components available for same-day shipping. Pasternack's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. This Pasternack SMP to SMP cable assembly has a female to female gender configuration with 50 ohm semi-rigid RG405 tinned coax. The PE3W08858LF SMP female to SMP female cable assembly operates to 18 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.4:1	

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	4.5	9	18	GHz
Insertion Loss (Typ.)	0.22	0.284	0.445	0.735	1.12	dB/ft
	0.72	0.93	1.46	2.41	3.67	dB/m

#### Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Female to SMP Female Cable Using Tinned RG405 Coax , LF Solder PE3W08858LF](#)

## SMP Female to SMP Female Cable Using Tinned RG405 Coax , LF Solder



### RF Cable Assemblies Technical Data Sheet

**PE3W08858LF**

#### Mechanical Specifications

##### Cable Assembly

Weight	0.025 lbs [11.34 g]
<b>Cable</b>	
Cable Type	RG405 Tinned
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Tinned Copper
One Time Minimum Bend Radius	0.05 in [1.27 mm]

##### Connectors

Description	Connector 1	Connector 2
Type	SMP Female	SMP Female
Specification	MIL-STD-348	MIL-STD-348
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Specification	MIL-G-45204	MIL-G-45204
Dielectric Type	PTFE	PTFE
Body Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Body Plating Specification	MIL-G-45204	MIL-G-45204

#### Environmental Specifications

##### Temperature

Operating Range -55 to +125 deg C

#### Compliance Certifications (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Female to SMP Female Cable Using Tinned RG405 Coax , LF Solder PE3W08858LF](#)

SMP Female to SMP Female Cable Using  
Tinned RG405 Coax , LF Solder




**RF Cable Assemblies Technical Data Sheet**

**PE3W08858LF**

**How to Order**

Part Number Configuration:



Example: PE3W08858LF-12 = 12 inches long cable  
PE3W08858LF-100cm = 100 cm long cable

SMP Female to SMP Female Cable Using Tinned RG405 Coax , LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Female to SMP Female Cable Using Tinned RG405 Coax , LF Solder PE3W08858LF](#)


URL: <https://www.pasternack.com/smp-female-to-smp-female-cable-using-tinned-rg405-lf-solder-pe3w08858lf-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W08858LF CAD Drawing

## SMP Female to SMP Female Cable Using Tinned RG405 Coax , LF Solder

ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	12/19/2022	HEAKKE	AGANWANI



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN WHOLE OR IN PART, WHETHER WRITTEN OR ELECTRONIC, IS PROHIBITED.

1