

MHV Female Bulkhead to MHV Female Bulkhead Cable Using RG58 Coax



RF Cable Assemblies Technical Data Sheet


PE3W08882

Configuration

- Connector 1: MHV Female Bulkhead
- Connector 2: MHV Female Bulkhead
- Cable Type: RG58

Features

- 65.9% Phase Velocity
- PVC (NC) Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W08882 MHV female bulkhead to MHV female bulkhead cable using RG58 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack MHV to MHV cable assembly has a female to female gender configuration with 50 ohm flexible RG58 coax. Our RF cable assembly with MHV bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		65.9		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Weight	1.689 lbs [766.12 g]
--------	----------------------

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MHV Female Bulkhead to MHV Female Bulkhead Cable Using RG58 Coax PE3W08882](#)



MHV Female Bulkhead to MHV Female Bulkhead Cable Using RG58 Coax

RF Cable Assemblies Technical Data Sheet

PE3W08882
Cable

Cable Type	RG58
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Tin
Dielectric Type	PE
Number of Shields	1
Shield Layer 1	Tinned Copper Braid
Jacket Material	PVC (NC), Black
Jacket Diameter	0.195 in [4.95 mm]
One Time Minimum Bend Radius	0.98 in [24.89 mm]
Repeated Minimum Bend Radius	1.96 in [49.78 mm]

Connectors

Description	Connector 1	Connector 2
Type	MHV Female Bulkhead	MHV Female Bulkhead
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 μ in minimum	30 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 μ in minimum	100 μ in minimum

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

 Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MHV Female Bulkhead to MHV Female Bulkhead Cable Using RG58 Coax PE3W08882](#)

MHV Female Bulkhead to MHV Female Bulkhead Cable Using RG58 Coax



RF Cable Assemblies Technical Data Sheet

PE3W08882

How to Order

Part Number Configuration:

PE3W08882

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W08882-12 = 12 inches long cable
PE3W08882-100cm = 100 cm long cable

MHV Female Bulkhead to MHV Female Bulkhead Cable Using RG58 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MHV Female Bulkhead to MHV Female Bulkhead Cable Using RG58 Coax PE3W08882](#)

URL: <https://www.pasternack.com/mhv-female-bulkhead-to-mhv-female-bulkhead-cable-using-rg58-pe3w08882-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W08882 CAD Drawing

MHV Female Bulkhead to MHV Female Bulkhead Cable Using RG58 Coax

