

BNC Female to SSMB Plug Cable Using RG316 Coax with HeatShrink



RF Cable Assemblies Technical Data Sheet



PE3W09360/HS

Configuration

- Connector 1: BNC Female
- Connector 2: SSMB Plug
- Cable Type: RG316

Features

- Max Frequency 3 GHz
- 69% Phase Velocity
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W09360/HS BNC female to SSMB plug cable using RG316 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack BNC to SSMB cable assembly has a female to plug gender configuration with 50 ohm flexible RG316 coax. The PE3W09360/HS BNC female to SSMB plug cable assembly operates to 3 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC Female to SSMB Plug Cable Using RG316 Coax with HeatShrink PE3W09360/HS](#)

BNC Female to SSMB Plug Cable Using RG316 Coax with HeatShrink



RF Cable Assemblies Technical Data Sheet

PE3W09360/HS

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		69		%
Operating Voltage (AC)			250	Vrms
Jacket Spark			2,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.11	0.16	0.238	0.38	0.58	dB/ft
	0.36	0.52	0.78	1.25	1.9	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Weight 0.039 lbs [17.69 g]

Cable

Cable Type RG316
Impedance 50 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Copper Clad Steel, Silver PTFE
Dielectric Type PTFE
Number of Shields 1
Shield Layer 1 Silver Plated Copper Braid
Jacket Material FEP, Tan
Jacket Diameter 0.102 in [2.59 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC Female to SSMB Plug Cable Using RG316 Coax with HeatShrink PE3W09360/HS](#)

BNC Female to SSMB Plug Cable Using RG316 Coax with HeatShrink



RF Cable Assemblies Technical Data Sheet

PE3W09360/HS

Connectors

Description	Connector 1	Connector 2
Type	BNC Female	SSMB Plug
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold
Contact Plating Specification		30 μ in minimum
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Nickel	Beryllium Copper, Gold
Outer Conductor Plating Specification		30 μ in minimum
Body Material and Plating	Brass, Nickel	Brass, Gold
Body Plating Specification		30 μ in minimum

Environmental Specifications

Temperature

Operating Range

-55 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC Female to SSMB Plug Cable Using RG316 Coax with HeatShrink PE3W09360/HS](#)

BNC Female to SSMB Plug Cable Using
RG316 Coax with HeatShrink




RF Cable Assemblies Technical Data Sheet

PE3W09360/HS

How to Order

Part Number Configuration:



Example: PE3W09360/HS-12 = 12 inches long cable
PE3W09360/HS-100cm = 100 cm long cable

BNC Female to SSMB Plug Cable Using RG316 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC Female to SSMB Plug Cable Using RG316 Coax with HeatShrink PE3W09360/HS](#)


URL: <https://www.pasternack.com/bnc-female-to-ssmb-plug-cable-using-rg316-with-heatshrink-pe3w09360-hs-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W09360/HS CAD Drawing

BNC Female to SSMB Plug Cable Using RG316 Coax with HeatShrink

ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
A		INITIAL RELEASE	01/27/2023	KDANG	AGAN/WANI



NOTES:

1. CABLE ASSY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROX CENTERED LONGER THAN 36 INCHES, TWO LABELS APPROX 6 INCHES FROM EACH CONNECTOR.
CABLES ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
- 2.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE