

SMP Female Right Angle to SMA Male
Cable Using PE-SR405FL Coax



RF Cable Assemblies Technical Data Sheet


PE3W07671

Configuration

- Connector 1: SMP Female Right Angle
- Connector 2: SMA Male
- Cable Type: PE-SR405FL

Features

- Max Frequency 3 GHz
- 69.5% Phase Velocity



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W07671 SMP female right angle to SMA male cable using PE-SR405FL coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack SMP to SMA cable assembly has a female to male gender configuration with 50 ohm formable PE-SR405FL coax. The PE3W07671 SMP female to SMA male cable assembly operates to 3 GHz. The right angle SMP interface on the PE-SR405FL cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Female Right Angle to SMA Male Cable Using PE-SR405FL Coax PE3W07671](#)



SMP Female Right Angle to SMA Male
Cable Using PE-SR405FL Coax

RF Cable Assemblies Technical Data Sheet

PE3W07671

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		69.5		%
Capacitance		29 [95.14]		pF/ft [pF/m]
DC Resistance Inner Conductor		65.7 [215.55]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		10.2 [33.46]		Ω/1000ft [Ω/Km]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	3			GHz
Insertion Loss (Typ.)	0.15	0.225	0.386			dB/ft
	0.49	0.74	1.27			dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2 for SMP Female connector and 0.04 xSQRT(FGHz) db for SMA Male connector.

Mechanical Specifications

Cable Assembly

Weight	0.021 lbs [9.53 g]
Cable	
Cable Type	PE-SR405FL
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor Material and Plating	Copper, Tin
Repeated Minimum Bend Radius	0.78 in [19.81 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Female Right Angle to SMA Male Cable Using PE-SR405FL Coax PE3W07671](#)

SMP Female Right Angle to SMA Male
Cable Using PE-SR405FL Coax



RF Cable Assemblies Technical Data Sheet

PE3W07671

Connectors

Description	Connector 1	Connector 2
Type	SMP Female Right Angle	SMA Male
Specification	DESC 94008	
Impedance	50 Ohms	50 Ohms
Mating Cycles		500
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Specification	MIL-G-45204	ASTM-B488
Dielectric Type	PTFE	PTFE
Body Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Body Plating Specification	MIL-G-45204	ASTM-B488
Coupling Nut Material and Plating		Steel
Torque		7 in-lbs [0.79 Nm]

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Female Right Angle to SMA Male Cable Using PE-SR405FL Coax PE3W07671](#)



SMP Female Right Angle to SMA Male Cable Using PE-SR405FL Coax

RF Cable Assemblies Technical Data Sheet

PE3W07671

How to Order

Part Number Configuration:

PE3W07671

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W07671-12 = 12 inches long cable
PE3W07671-100cm = 100 cm long cable

SMP Female Right Angle to SMA Male Cable Using PE-SR405FL Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Female Right Angle to SMA Male Cable Using PE-SR405FL Coax PE3W07671](#)

URL: <https://www.pasternack.com/smp-female-right-angle-to-sma-male-cable-using-pe-sr405fl-pe3w07671-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W07671 CAD Drawing

SMP Female Right Angle to SMA Male Cable Using PE-SR405FL Coax

