



Reverse Polarity TNC Male to N Female Bulkhead Low
Loss Cable 60 Inch Length Using LMR-240 Coax

RF Cable Assemblies Technical Data Sheet


PE3W09859-60

Configuration

- Connector 1: TNC Male Reverse Polarity
- Connector 2: N Female Bulkhead
- Cable Type: LMR-240

Features

- Max Frequency 5.8 GHz
- Shielding Effectivity > 90 dB
- 84% Phase Velocity
- Double Shielded
- PE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W09859-60 reverse polarity TNC male to type N female bulkhead 60 inch cable using LMR-240 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack reverse polarity TNC to type N cable assembly has a male to female gender configuration with 50 ohm flexible LMR-240 coax. The PE3W09859-60 reverse polarity TNC male to type N female cable assembly operates to 5.8 GHz. Our RF cable assembly with type N bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity TNC Male to N Female Bulkhead Low Loss Cable 60 Inch Length Using LMR-240 Coax PE3W09859-60](#)



Reverse Polarity TNC Male to N Female Bulkhead Low Loss Cable 60 Inch Length Using LMR-240 Coax

RF Cable Assemblies Technical Data Sheet

PE3W09859-60

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.45:1	
Velocity of Propagation		84		%
RF Shielding	90			dB
Group Delay		1.21 [3.97]		ns/ft [ns/m]
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		3.2 [10.5]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		3.89 [12.76]		Ω/1000ft [Ω/Km]
Jacket Spark			5,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	5.8	GHz
Insertion Loss (Typ.)	0.4	0.5	0.6	0.85	1.2	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Length*	60 in [152.4 cm]
Diameter	0.81 in [20.57 mm]

Cable

Cable Type	LMR-240
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.24 in [6.1 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity TNC Male to N Female Bulkhead Low Loss Cable 60 Inch Length Using LMR-240 Coax PE3W09859-60](#)



Reverse Polarity TNC Male to N Female Bulkhead Low
Loss Cable 60 Inch Length Using LMR-240 Coax

RF Cable Assemblies Technical Data Sheet

PE3W09859-60

One Time Minimum Bend Radius	0.75 in [19.05 mm]
Repeated Minimum Bend Radius	2.5 in [63.5 mm]
Bending Moment	0.25 lbs-ft [0.34 N-m]
Flat Plate Crush	20 lbs/in [0.36 Kg/mm]
Tensile Strength	80 lbs [36.29 Kg]

Connectors

Description	Connector 1	Connector 2
Type	TNC Male Reverse Polarity	N Female Bulkhead
Specification		MIL-STD-348
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	
Contact Material and Plating	Phosphor Bronze, Gold	Beryllium Copper, Gold
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating		Brass, Tri-Metal
Body Material and Plating	Brass, Nickel	Brass, Tri-Metal
Coupling Nut Material and Plating	Brass, Nickel	

Environmental Specifications

Temperature

Operating Range	-40 to +85 deg C
-----------------	------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity TNC Male to N Female Bulkhead Low Loss Cable 60 Inch Length Using LMR-240 Coax PE3W09859-60](#)



Reverse Polarity TNC Male to N Female Bulkhead Low Loss Cable 60 Inch Length Using LMR-240 Coax

RF Cable Assemblies Technical Data Sheet

PE3W09859-60

How to Order

Part Number Configuration:

PE3W09859

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W09859-12 = 12 inches long cable
PE3W09859-100cm = 100 cm long cable

Reverse Polarity TNC Male to N Female Bulkhead Low Loss Cable 60 Inch Length Using LMR-240 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity TNC Male to N Female Bulkhead Low Loss Cable 60 Inch Length Using LMR-240 Coax PE3W09859-60](https://www.pasternack.com/tnc-male-n-female-lmr240-cable-assembly-pe3w09859-60-p.aspx)

URL: <https://www.pasternack.com/tnc-male-n-female-lmr240-cable-assembly-pe3w09859-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Reverse Polarity TNC Male to N Female Bulkhead Low Loss Cable 60 Inch Length Using LMR-240 Coax

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/16/2020	S.ELLIS



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS	TOLERANCES:		THIRD-ANGLE PROJECTION	
	X = ± .2 [5.08] XX = ± .02 [.51] XXX = ± .005 [.13]	FRACTIONS = 1/32 ANGLES ± °		
PE PASTERNAK® an INFINITE® brand				
Pasternack Enterprises, Inc. P.O. Box 16759, Irvine, CA 92623. Phone: 1.949.261.1920 / 1.866.727.8376 Fax: 1.949.261.7451 Website: www.pasternack.com E-mail: sales@pasternack.com				
SIZE		CAGE CODE	DRAWN BY	ITEM NO.
A		53919	K.DANG	PE3W09859
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.				
CABLE LENGTH (L) TOLERANCES: $L \leq 12$ [305] = +1 [25] / -0 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0 120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 300 [7620] < L = +5% / -0				
SCALE		1 OF 1		REV
A		N/A		A

WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.