

SMC Plug Right Angle to SMB Plug Cable Using RG174 Coax with HeatShrink, LF Solder



RF Cable Assemblies Technical Data Sheet


PE3W08236LF/HS

Configuration

- Connector 1: SMC Plug Right Angle
- Connector 2: SMB Plug
- Cable Type: RG174

Features

- Max Frequency 1 GHz
- 66% Phase Velocity
- PVC Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W08236LF/HS SMC plug right angle to SMB plug cable using RG174 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMC to SMB cable assembly has a plug to plug gender configuration with 50 ohm flexible RG174 coax. The PE3W08236LF/HS SMC plug to SMB plug cable assembly operates to 1 GHz. The right angle SMC interface on the RG174 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMC Plug Right Angle to SMB Plug Cable Using RG174 Coax with HeatShrink, LF Solder PE3W08236LF/HS](#)



SMC Plug Right Angle to SMB Plug Cable Using
RG174 Coax with HeatShrink, LF Solder

RF Cable Assemblies Technical Data Sheet

PE3W08236LF/HS

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Velocity of Propagation		66		%
Capacitance		31.08 [101.97]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	500	1,000	MHz
Insertion Loss (Typ.)	0.042	0.084	0.137	0.211	0.319	dB/ft
	0.14	0.28	0.45	0.69	1.05	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2 dB for the right angle connector and 0.1 dB for the straight connector.

Mechanical Specifications

Cable Assembly

Cable

Cable Type	RG174
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel
Dielectric Type	PE
Number of Shields	1
Shield Layer 1	Tinned Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.11 in [2.79 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMC Plug Right Angle to SMB Plug Cable Using RG174 Coax with HeatShrink, LF Solder PE3W08236LF/HS](#)



SMC Plug Right Angle to SMB Plug Cable Using
RG174 Coax with HeatShrink, LF Solder

RF Cable Assemblies Technical Data Sheet

PE3W08236LF/HS

Connectors

Description	Connector 1	Connector 2
Type	SMC Plug Right Angle	SMB Plug
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Specification	30 µin minimum	30 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin minimum	100 µin minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	100 µin minimum	100 µin minimum
Hex Size	1/4 inch	
Torque	3 in-lbs [0.34 Nm]	

Environmental Specifications

Temperature

Operating Range

-40 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMC Plug Right Angle to SMB Plug Cable Using RG174 Coax with HeatShrink, LF Solder PE3W08236LF/HS](#)



SMC Plug Right Angle to SMB Plug Cable Using RG174 Coax with HeatShrink, LF Solder

RF Cable Assemblies Technical Data Sheet

PE3W08236LF/HS

How to Order

Part Number Configuration:

PE3W08236LF/HS - xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W08236LF/HS-12 = 12 inches long cable
PE3W08236LF/HS-100cm = 100 cm long cable

SMC Plug Right Angle to SMB Plug Cable Using RG174 Coax with HeatShrink, LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMC Plug Right Angle to SMB Plug Cable Using RG174 Coax with HeatShrink, LF Solder PE3W08236LF/HS](#)

URL:

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W08236LF/HS CAD Drawing

SMC Plug Right Angle to SMB Plug Cable Using RG174 Coax with HeatShrink, LF Solder



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT:
36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED.
LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY
6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
		SCALE	SHEET
		NONE	1 OF 1
DESCRIPTION SMC PLUG RIGHT ANGLE TO SMB PLUG CABLE USING RG174 COAX WITH HEATSHRINK, LF SOLDER			
UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		Website: www.Pasternack.com Phone: 1.866.727.8376 1.949.261.1920	
PE PASTERNAK an INFINITO brand			
TOLERANCES:			
X = ±.2 [.5] FRACTIONS .XX = ±.02 [.3] XXX = ±.005 [.13] ANGLES ±°			
CABLE LENGTH TOLERANCES:			
>12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0			
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.			
SIZE	CAGE CODE	DRAWN BY	ITEM NO.
A	53919	DMAY	PE3W08236LF/HS
			REV
			A