

BNC Male to BNC Male Cable Using LMR-240-UF Coax



RF Cable Assemblies Technical Data Sheet


PE3W08340

Configuration

Connector 1: BNC MaleConnector 2: BNC MaleCable Type: LMR-240-UF

Features

- Max Frequency 1 GHz
- Shielding Effectivity > 90 dB
- 84% Phase Velocity
- · Double Shielded
- TPE Jacket



Applications

· General Purpose

· Laboratory Use

Description

Pasternack's PE3W08340 BNC male to BNC male cable using LMR-240-UF coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack BNC to BNC cable assembly has a male to male gender configuration with 50 ohm flexible LMR-240-UF coax. The PE3W08340 BNC male to BNC male cable assembly operates to 1 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: BNC Male to BNC Male Cable Using LMR-240-UF Coax PE3W08340

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451



Wall I was a second

BNC Male to BNC Male Cable Using LMR-240-UF Coax

RF Cable Assemblies Technical Data Sheet

PE3W08340

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR		7.00	1.4:1	
Velocity of Propagation		84		%
RF Shielding	90			dB
Group Delay		1.21 [3.97]		ns/ft [ns/m]
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		4.28 [14.04]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		3.89 [12.76]		Ω/1000ft [Ω/Km]
Jacket Spark			5,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	500	1,000	MHz
Insertion Loss (Max.)	0.021 0.07	0.029 0.1	0.047 0.15	0.067 0.22	0.096 0.31	dB/ft dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per BNC male connector.

Mechanical Specifications

Cable Assembly

Diameter 0.56 in [14.22 mm]

Cable

Cable Type

Impedance

Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type

Number of Shields

Chief Inner Conductor

Alwaying Table

LMR-240-UF

50 Ohms

Stranded

Copper

PE (F)

Number of Shields

Shield Layer 1 Aluminum Tape
Shield Layer 2 Tinned Copper Braid
Jacket Material TPE, Black

Jacket MaterialTPE, BlackJacket Diameter0.24 in [6.1 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: BNC Male to BNC Male Cable Using LMR-240-UF Coax PE3W08340

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



931, RED

BNC Male to BNC Male Cable Using LMR-240-UF Coax

RF Cable Assemblies Technical Data Sheet

PE3W08340

One Time Minimum Bend Radius Repeated Minimum Bend Radius Bending Moment Flat Plate Crush Tensile Strength 0.75 in [19.05 mm] 2.5 in [63.5 mm] 0.13 lbs-ft [0.18 N-m] 13 lbs/in [0.23 Kg/mm] 80 lbs [36.29 Kg]

Connectors

Connector 1	Connector 2	
BNC Male	BNC Male	
50 Ohms	50 Ohms	
Brass, Gold	Brass, Gold	
Teflon	Teflon	
Beryllium Copper, Silver	Beryllium Copper, Silver	
Brass, Silver	Brass, Silver	
Brass, Silver	Brass, Silver	
Silicone	Silicone	
	BNC Male 50 Ohms Brass, Gold Teflon Beryllium Copper, Silver Brass, Silver Brass, Silver	

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: BNC Male to BNC Male Cable Using LMR-240-UF Coax PE3W08340

PE3W08340 REV 1.0

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451



BNC Male to BNC Male Cable Using LMR-240-UF Coax



RF Cable Assemblies Technical Data Sheet

PE3W08340

How to Order



Example: PE3W08340-12 = 12 inches long cable

PE3W08340-100cm = 100 cm long cable

BNC Male to BNC Male Cable Using LMR-240-UF Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: BNC Male to BNC Male Cable Using LMR-240-UF Coax PE3W08340

URL: https://www.pasternack.com/bnc-male-bnc-male-lmr240uf-cable-assembly-pe3w08340-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE3W08340 CAD DrawingBNC Male to BNC Male Cable Using LMR-240-UF Coax

