

TNC Male Right Angle to N Male Right Angle Low Loss  
Cable Using LMR-400 Coax With Times Microwave  
Parts with HeatShrink and 180 Deg. Clock




## RF Cable Assemblies Technical Data Sheet

**PE3W10718/SP1**


### Configuration

- Connector 1: TNC Male Right Angle
- Connector 2: N Male Right Angle
- Cable Type: LMR-400



### Features

- Max Frequency 6 GHz
- Shielding Effectivity > 90 dB
- 85% Phase Velocity
- Double Shielded
- PE Jacket



### Applications

- General Purpose
- Laboratory Use

### Description

Pasternack's PE3W10718/SP1 TNC male right angle to type N male right angle cable using LMR-400 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TNC to type N cable assembly has a male to male gender configuration with 50 ohm flexible LMR-400 coax. The PE3W10718/SP1 TNC male to type N male cable assembly operates to 6 GHz. The right angle TNC and right angle type N interfaces on the LMR-400 cable allow for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male Right Angle to N Male Right Angle Low Loss Cable Using LMR-400 Coax With Times Microwave Parts with HeatShrink and 180 Deg. Clock PE3W10718/SP1](#)

TNC Male Right Angle to N Male Right Angle Low Loss  
Cable Using LMR-400 Coax With Times Microwave  
Parts with HeatShrink and 180 Deg. Clock



## RF Cable Assemblies Technical Data Sheet

**PE3W10718/SP1**

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		85		%
RF Shielding	90			dB
Group Delay		1.2 [3.94]		ns/ft [ns/m]
Capacitance		23.9 [78.41]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		1.39 [4.56]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		1.65 [5.41]		Ω/1000ft [Ω/Km]
Jacket Spark			8,000	Vrms

### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	5.8	GHz
Insertion Loss (Typ.)	0.02	0.028	0.041	0.068	0.108	dB/ft
	0.07	0.09	0.13	0.22	0.35	dB/m

#### Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2 dB per connector.

### Mechanical Specifications

#### Cable Assembly

Weight 0.38 lbs [172.37 g]

#### Cable

Cable Type LMR-400  
Impedance 50 Ohms  
Inner Conductor Type Solid  
Inner Conductor Material and Plating Copper Clad Aluminum  
Dielectric Type PE (F)  
Number of Shields 2  
Shield Layer 1 Aluminum Tape  
Shield Layer 2 Tinned Copper Braid  
Jacket Material PE, Black  
Jacket Diameter 0.405 in [10.29 mm]

One Time Minimum Bend Radius 1 in [25.4 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male Right Angle to N Male Right Angle Low Loss Cable Using LMR-400 Coax With Times Microwave Parts with HeatShrink and 180 Deg. Clock PE3W10718/SP1](#)

TNC Male Right Angle to N Male Right Angle Low Loss  
Cable Using LMR-400 Coax With Times Microwave  
Parts with HeatShrink and 180 Deg. Clock



## RF Cable Assemblies Technical Data Sheet

**PE3W10718/SP1**

Repeated Minimum Bend Radius	4 in [101.6 mm]
Bending Moment	0.5 lbs-ft [0.68 N-m]
Flat Plate Crush	40 lbs/in [0.71 Kg/mm]
Tensile Strength	160 lbs [72.57 Kg]

### Connectors

Description	Connector 1	Connector 2
Type	TNC Male Right Angle	N Male Right Angle
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Silver	Beryllium Copper, Gold
Contact Plating Specification		1.27 $\mu$ m minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Silver	Brass, Tri-Metal
Body Plating Specification		2 $\mu$ m minimum
Coupling Nut Material and Plating	Brass, Silver	Brass, Tri-Metal
Coupling Nut Plating Specification		2 $\mu$ m minimum
Torque		44 in-lbs [4.97 Nm]

### Environmental Specifications

#### Temperature

Operating Range

-40 to +85 deg C

### Compliance Certifications (see [product page](#) for current document)

### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male Right Angle to N Male Right Angle Low Loss Cable Using LMR-400 Coax With Times Microwave Parts with HeatShrink and 180 Deg. Clock PE3W10718/SP1](#)



TNC Male Right Angle to N Male Right Angle Low Loss  
Cable Using LMR-400 Coax With Times Microwave  
Parts with HeatShrink and 180 Deg. Clock

## RF Cable Assemblies Technical Data Sheet

**PE3W10718/SP1**

### How to Order

Part Number Configuration:

**PE3W10718/SP1**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3W10718/SP1-12 = 12 inches long cable  
PE3W10718/SP1-100cm = 100 cm long cable

TNC Male Right Angle to N Male Right Angle Low Loss Cable Using LMR-400 Coax With Times Microwave Parts with HeatShrink and 180 Deg. Clock from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male Right Angle to N Male Right Angle Low Loss Cable Using LMR-400 Coax With Times Microwave Parts with HeatShrink and 180 Deg. Clock PE3W10718/SP1](#)

URL: <https://www.pasternack.com/tnc-male-right-angle-to-n-male-low-loss-cable-using-lmr-400-with-heatshrink-and-180-deg.-clock-pe3w10718-sp1-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3W10718/SP1 CAD Drawing

TNC Male Right Angle to N Male Right Angle Low Loss Cable Using LMR-400 Coax  
With Times Microwave Parts with HeatShrink and 180 Deg. Clock

