



SMA Male to SMA Female Bulkhead Cable Using Tinned RG402 Coax

TECHNICAL DATA SHEET

PE3W09308

Configuration


- Connector 1: SMA Male
- Connector 2: SMA Female Bulkhead
- Cable Type: RG402 Tinned
- Coax Flex Type: Semi-Rigid

Features

- Max Frequency 18 GHz

Applications

- General Purpose
- Laboratory Use



Description

Pasternack's PE3W09308 SMA male to SMA female bulkhead cable using tinned RG402 coax is part of our full line of RF components available for same-day shipping. Pasternack's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. This Pasternack SMA to SMA cable assembly has a male to female gender configuration with 50 ohm semi-rigid RG402 tinned coax. The PE3W09308 SMA male to SMA female cable assembly operates to 18 GHz. Our RF cable assembly with SMA bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Female Bulkhead Cable Using Tinned RG402 Coax PE3W09308](#)



SMA Male to SMA Female Bulkhead Cable Using Tinned RG402 Coax

TECHNICAL DATA SHEET

PE3W09308

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	1000	2000	4500	9000	#####	MHz	
PE3W09308	Custom Lengths Available	Insertion Loss (Typ.)	0.12	0.15	0.24	0.41	0.65	dB/ft	
			0.4	0.5	0.79	1.35	2.14	dB/m	
PE3W09308-6	6 inch	Insertion Loss (Typ.)	0.26	0.28	0.32	0.41	0.53	dB	0.031
PE3W09308-12	12 inch	Insertion Loss (Typ.)	0.32	0.35	0.44	0.61	0.85	dB	0.046
PE3W09308-18	18 inch	Insertion Loss (Typ.)	0.38	0.43	0.56	0.82	1.18	dB	0.062
PE3W09308-24	24 inch	Insertion Loss (Typ.)	0.44	0.5	0.68	1.02	1.5	dB	0.078
PE3W09308-36	36 inch	Insertion Loss (Typ.)	0.56	0.65	0.92	1.43	2.15	dB	0.109

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB

Loss due to Connector 2: 0.1 dB

Base Weight: 0.046 pounds

Additional Weight per Inch: 0.00259 pounds

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Weight 0.046 lbs [20.87 g]

Cable

Cable Type RG402 Tinned
Impedance 50 Ohms
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper Clad Steel, Silver
Dielectric Type PTFE
Number of Shields 1
Shield Layer 1 Tinned Copper

One Time Minimum Bend Radius 1 in [25.4 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Female Bulkhead Cable Using Tinned RG402 Coax PE3W09308](#)



SMA Male to SMA Female Bulkhead Cable Using Tinned RG402 Coax

TECHNICAL DATA SHEET

PE3W09308

Connectors

Description	Connector 1	Connector 2
Type	SMA Male Threaded	SMA Female Bulkhead Threaded
Specification	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold over Nickel
Contact Plating Specification	50 μ in minimum	
Dielectric Type	PTFE	PTFE
Body Material and Plating	Stainless Steel, Gold	Brass, Gold over Nickel
Body Plating Specification	10 μ in minimum	
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100 μ in minimum	
Hex Size	5/16 inch	
Torque	3 in-lbs [0.34 Nm]	

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Female Bulkhead Cable Using Tinned RG402 Coax PE3W09308](#)



SMA Male to SMA Female Bulkhead Cable Using Tinned RG402 Coax

TECHNICAL DATA SHEET

PE3W09308

How to Order

Part Number Configuration:

PE3W09308- **xx****uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W09308-12 = 12 inches long cable
PE3W09308-100cm = 100 cm long cable

SMA Male to SMA Female Bulkhead Cable Using Tinned RG402 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Female Bulkhead Cable Using Tinned RG402 Coax PE3W09308](#)

URL: <https://www.pasternack.com/sma-male-sma-female-tinned-rg402-cable-assembly-pe3w09308-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

