



MCX Plug to SSMA Male Cable Using RG316 Coax

RF Cable Assemblies Technical Data Sheet



PE3W09557

Configuration

- Connector 1: MCX Plug
- Connector 2: SSMA Male
- Cable Type: RG316

Features

- Max Frequency 3 GHz
- 69% Phase Velocity
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W09557 MCX plug to SSMA male cable using RG316 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack MCX to SSMA cable assembly has a plug to male gender configuration with 50 ohm flexible RG316 coax. The PE3W09557 MCX plug to SSMA male cable assembly operates to 3 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MCX Plug to SSMA Male Cable Using RG316 Coax PE3W09557](#)



MCX Plug to SSMA Male Cable Using RG316 Coax

RF Cable Assemblies Technical Data Sheet

PE3W09557

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		69		%
Operating Voltage (AC)			250	Vrms
Jacket Spark			2,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.16	0.238	0.38	0.53	0.58	dB/ft
	0.52	0.78	1.25	1.74	1.9	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Weight 0.029 lbs [13.15 g]

Cable

Cable Type RG316
 Impedance 50 Ohms
 Inner Conductor Type Stranded
 Inner Conductor Material and Plating Copper Clad Steel, Silver PTFE
 Dielectric Type PTFE
 Number of Shields 1
 Shield Layer 1 Silver Plated Copper Braid
 Jacket Material FEP, Tan
 Jacket Diameter 0.102 in [2.59 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MCX Plug to SSMA Male Cable Using RG316 Coax PE3W09557](#)



MCX Plug to SSMA Male Cable Using RG316 Coax

RF Cable Assemblies Technical Data Sheet

PE3W09557

Connectors

Description	Connector 1	Connector 2
Type	MCX Plug	SSMA Male
Specification	CECC 22220	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 μ in minimum	50 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 μ in minimum	100 μ in minimum
Coupling Nut Material and Plating		Brass, Nickel
Coupling Nut Plating Specification		100 μ in minimum
Hex Size		1/4 inch

Environmental Specifications

Temperature

Operating Range

-55 to +155 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MCX Plug to SSMA Male Cable Using RG316 Coax PE3W09557](#)

MCX Plug to SSMA Male Cable Using RG316 Coax



RF Cable Assemblies Technical Data Sheet

PE3W09557

How to Order

Part Number Configuration:

PE3W09557

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W09557-12 = 12 inches long cable
PE3W09557-100cm = 100 cm long cable

MCX Plug to SSMA Male Cable Using RG316 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MCX Plug to SSMA Male Cable Using RG316 Coax PE3W09557](#)

URL: <https://www.pasternack.com/mcx-plug-to-ssma-male-cable-using-rg316-pe3w09557-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W09557 CAD Drawing

ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	01/12/2023	HBKKE	AGANWAN



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.

 PASTERNACK® an INFINITI® brand			INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE SHEET	
	[5] FRACTIONS	± 1/32 [1.5] [5.13]	ANGLES ± 1° [5] [5.13]	INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE SHEET
OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES DIMENSIONS IN [] ARE MILLIMETERS TOLERANCES:	2 [5] [5.13]	WEBSITE: www.Pasternack.com PHONE: 1.866.727.8376 1.949.261.1920	1 OF 1 NONE	MCX PLUG TO SSMA MALE CABLE USING RG316 COAX
DESCRIPTION	ITEM NO. PE3W09557	DRAWN BY HBAKKE	SIZE CAGE CODE A 53919	REV A
>1[2.805] = +1[25] / -0 [5] ≤ 60 [162] = +2 [51] / -0 [5] ≤ 300 [3048] = +4 [102] / -0 [3] ≤ 20 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES DIMENSIONS IN [] ARE MILLIMETERS TOLERANCES:				