



75 Ohm F Male to 75 Ohm F Male Cable Using
75 Ohm RG179 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE3W09571/HS

Configuration

- Connector 1: F Male
- Connector 2: F Male
- Cable Type: RG179

Features

- Max Frequency 1 GHz
- 70% Phase Velocity
- FEP Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W09571/HS 75 ohm type F male to 75 ohm type F male cable using 75 ohm RG179 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type F to type F cable assembly has a male to male gender configuration with 75 ohm flexible RG179 coax. The PE3W09571/HS type F male to type F male cable assembly operates to 1 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm F Male to 75 Ohm F Male Cable Using 75 Ohm RG179 Coax with HeatShrink PE3W09571/HS](#)



75 Ohm F Male to 75 Ohm F Male Cable Using
75 Ohm RG179 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE3W09571/HS

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Velocity of Propagation		70		%
Capacitance		19.4 [63.65]		pF/ft [pF/m]
Operating Voltage (AC)			500	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	100	250	500	1,000		MHz
Insertion Loss (Typ.)	0.09	0.137	0.203	0.3		dB/ft
	0.3	0.45	0.67	0.98		dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Weight 0.029 lbs [13.15 g]

Cable

Cable Type RG179
Impedance 75 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Copper Clad Steel, Silver
Dielectric Type PTFE
Number of Shields 1
Shield Layer 1 Silver Plated Copper Braid
Jacket Material FEP, Tan
Jacket Diameter 0.1 in [2.54 mm]
Repeated Minimum Bend Radius 0.4 in [10.16 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm F Male to 75 Ohm F Male Cable Using 75 Ohm RG179 Coax with HeatShrink PE3W09571/HS](#)



75 Ohm F Male to 75 Ohm F Male Cable Using
75 Ohm RG179 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE3W09571/HS

Connectors

Description	Connector 1	Connector 2
Type	F Male	F Male
Impedance	75 Ohms	75 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Hex Size	7/16 inch	7/16 inch
Torque	12 in-lbs [1.36 Nm]	12 in-lbs [1.36 Nm]

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm F Male to 75 Ohm F Male Cable Using 75 Ohm RG179 Coax with HeatShrink PE3W09571/HS](#)



75 Ohm F Male to 75 Ohm F Male Cable Using
75 Ohm RG179 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE3W09571/HS

How to Order

Part Number Configuration:

PE3W09571/HS

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W09571/HS-12 = 12 inches long cable
PE3W09571/HS-100cm = 100 cm long cable


75 Ohm F Male to 75 Ohm F Male Cable Using 75 Ohm RG179 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm F Male to 75 Ohm F Male Cable Using 75 Ohm RG179 Coax with HeatShrink PE3W09571/HS](https://www.pasternack.com/75-ohm-f-male-to-75-ohm-f-male-cable-using-rg179-with-heatshrink-pe3w09571-hs-p.aspx)

URL: <https://www.pasternack.com/75-ohm-f-male-to-75-ohm-f-male-cable-using-rg179-with-heatshrink-pe3w09571-hs-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

75 Ohm F Male to 75 Ohm F Male Cable Using 75 Ohm RG179 Coax with HeatShrink



—RG179B/U CABLE

LABEL

SEE NOTE 1

— 2X HEAT SHRINK



11mm
HEX

2X 75 OHM
F MALE
CONNECTOR

NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS , ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN WHOLE OR PART WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS	 		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
	PE PASTERNAK® an INFINITO brand		SCALE	SHEET
	Website: www.Pasternak.com Phone: 1.866.727.8376 1.949.261.1920		NONE	1 OF 1
DESCRIPTION				
75 Ohm F Male to 75 Ohm F Male Cable Using 75 Ohm RG179 Coax with HeatShrink				
SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	53919	BPUC/HASKI	PE3W09571/HS	A
ALL DIMENSIONS ARE FOR REFERENCE ONLY (AND SUBJECT TO CHANGE WITHOUT NOTICE)				