

Reverse Polarity TNC Jack Bulkhead to SSMC Plug Cable Using RG188 Coax, LF Solder





PE3W10615LF

Configuration

- Connector 1: TNC Jack Reverse Polarity Bulkhead
- Connector 2: SSMC Plug
- Cable Type: RG188
- Coax Flex Type: Flexible

Features

- Max Frequency 3 GHz
- PTFE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W10615LF reverse polarity TNC jack bulkhead to SSMC plug cable using RG188 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack reverse polarity TNC to SSMC cable assembly has a jack to plug gender configuration with 50 ohm flexible RG188 coax. The PE3W10615LF reverse polarity TNC jack to SSMC plug cable assembly operates to 3 GHz. Our RF cable assembly with TNC bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	

Specifications by Frequency

Reverse Polarity TNC Jack Bulkhead to SSMC Plug Cable Using RG188 Coax, LF Solder



PE3W10615LF

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	100	250	500	1000	3000	MHz	
PE3W10615LF	Custom Lengths Available	Insertion Loss (Typ.)	0.05	0.125	0.25	0.5	1.5	dB/ft	
			0.17	0.42	0.83	1.65	4.93	dB/m	
PE3W10615LF-12	12 inch	Insertion Loss (Typ.)	0.45	0.53	0.65	0.9	1.9	dB	0.055
PE3W10615LF-24	24 inch	Insertion Loss (Typ.)	0.5	0.65	0.9	1.4	3.4	dB	0.066
PE3W10615LF-36	36 inch	Insertion Loss (Typ.)	0.55	0.78	1.15	1.9	4.9	dB	0.076
PE3W10615LF-48	48 inch	Insertion Loss (Typ.)	0.6	0.9	1.4	2.4	6.4	dB	0.086
PE3W10615LF-72	72 inch	Insertion Loss (Typ.)	0.7	1.15	1.9	3.4	9.4	dB	0.106

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB
 Loss due to Connector 2: 0.3 dB
 Base Weight: 0.055 pounds
 Additional Weight per Inch: 0.00084 pounds

Mechanical Specifications

Cable Assembly

Weight 0.055 lbs [24.95 g]

Cable

Cable Type	RG188
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	PTFE, White
Jacket Diameter	0.11 in [2.79 mm]

Reverse Polarity TNC Jack Bulkhead to SSMC Plug Cable Using RG188 Coax, LF Solder



PE3W10615LF

Connectors

Description	Connector 1	Connector 2
Type	TNC Jack Reverse Polarity Bulkhead	SSMC Plug
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Mating Cycles		500
Contact Material and Plating	Phosphor Bronze, Gold	Beryllium Copper, Gold
Contact Plating Specification	30 μ in minimum	MIL-G-45204
Dielectric Type	PTFE	Teflon
Body Material and Plating	Brass, Nickel	Beryllium Copper, Gold
Body Plating Specification		MIL-G-45204
Coupling Nut Material and Plating		Beryllium Copper, Gold
Coupling Nut Plating Specification		MIL-G-45206
Torque		1.75 in-lbs 0.2 Nm

Environmental Specifications

Operating Range Temperature -55 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Reverse Polarity TNC Jack Bulkhead to SSMC Plug Cable Using RG188 Coax, LF Solder




PE3W10615LF

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3W10615LF-12 = 12 inches long cable
PE3W10615LF-100cm = 100 cm long cable

Reverse Polarity TNC Jack Bulkhead to SSMC Plug Cable Using RG188 Coax, LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity TNC Jack Bulkhead to SSMC Plug Cable Using RG188 Coax, LF Solder PE3W10615LF](#)

URL: <https://www.pasternack.com/reverse-polarity-tnc-jack-bulkhead-to-ssmc-plug-cable-using-rg188-lf-solder-pe3w10615lf-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W10615LF CAD Drawing

Reverse Polarity TNC Jack Bulkhead to SSMC Plug Cable Using RG188 Coax, LF Solder



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE ARE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVISION CONTRARY TO U.S. LAW PROHIBITED.

PE DS Rev-D4 As26