

N Male Right Angle to N Female Bulkhead Cable Using RG142 Coax

PE3W15225




Configuration

- Connector 1: N Male Right Angle
- Connector 2: N Female Bulkhead
- Cable Type: RG142
- Coax Flex Type: Flexible

Features

- Max Frequency 1 GHz
- 70% Phase Velocity
- Double Shielded
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W15225 type N male right angle to type N female bulkhead cable using RG142 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to type N cable assembly has a male to female gender configuration with 50 ohm flexible RG142 coax. The PE3W15225 type N male to type N female cable assembly operates to 1 GHz. The right angle type N interface on the RG142 cable allows for easier connections in tight spaces. Our RF cable assembly with type N bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1	GHz
VSWR			1.4:1	
Velocity of Propagation	70			%
Capacitance	29.4 [96.46]			pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

Specifications by Frequency

N Male Right Angle to N Female Bulkhead Cable Using RG142 Coax



PE3W15225

Part Number	Length	Description	F1	F2	F3	F4	Units	Weight (lbs)
			Frequency	100	250	500	1000	
PE3W15225	Custom Lengths Available	Insertion Loss (Typ.)	0.04	0.06	0.087	0.129	dB/ft	
			0.13	0.2	0.29	0.43	dB/m	
PE3W15225-12	12 inch	Insertion Loss (Typ.)	0.34	0.36	0.39	0.43	dB	0.254
PE3W15225-24	24 inch	Insertion Loss (Typ.)	0.38	0.42	0.48	0.56	dB	0.296
PE3W15225-36	36 inch	Insertion Loss (Typ.)	0.42	0.48	0.57	0.69	dB	0.338
PE3W15225-48	48 inch	Insertion Loss (Typ.)	0.46	0.54	0.65	0.82	dB	0.38
PE3W15225-60	60 inch	Insertion Loss (Typ.)	0.5	0.6	0.74	0.95	dB	0.422

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.2 dB

Loss due to Connector 2: 0.1 dB

Base Weight: 0.254 pounds

Additional Weight per Inch: 0.0035 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter 0.5 in [12.7 mm]
Weight 0.254 lbs [115.21 g]

Cable

Cable Type	RG142
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.195 in [4.95 mm]
Repeated Minimum Bend Radius	1 in [25.4 mm]

N Male Right Angle to N Female Bulkhead Cable Using RG142 Coax



PE3W15225

Connectors

Description	Connector 1	Connector 2
Type	N Male Right Angle	N Female Bulkhead
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 μ in minimum	30 μ in minimum
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating		Brass, Nickel
Outer Conductor Plating Specification		100 μ in minimum
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 μ in minimum	100 μ in minimum
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100 μ in minimum	

Environmental Specifications

Operating Range Temperature -55 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

N Male Right Angle to N Female Bulkhead Cable Using RG142 Coax




PE3W15225

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3W15225-12 = 12 inches long cable
PE3W15225-100cm = 100 cm long cable

N Male Right Angle to N Female Bulkhead Cable Using RG142 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male Right Angle to N Female Bulkhead Cable Using RG142 Coax PE3W15225](#)

URL: <https://www.pasternack.com/n-male-right-angle-to-n-female-bulkhead-cable-using-rg142-pe3w15225-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W15225 CAD Drawing

N Male Right Angle to N Female Bulkhead Cable Using RG142 Coax

