



Reverse Polarity SMA Plug Right Angle to Reverse Polarity
BNC Plug Right Angle Low Loss Cable Using LMR-195 Coax

RF Cable Assemblies Technical Data Sheet


PE3W10794

Configuration

- Connector 1: SMA Plug Reverse Polarity Right Angle
- Connector 2: BNC Plug Reverse Polarity Right Angle
- Cable Type: LMR-195

Features

- Shielding Effectivity > 90 dB
- 80% Phase Velocity
- Double Shielded
- PE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W10794 reverse polarity SMA plug right angle to reverse polarity BNC plug right angle cable using LMR-195 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack reverse polarity SMA to reverse polarity BNC cable assembly has a plug to plug gender configuration with 50 ohm flexible LMR-195 coax. The right angle SMA and right angle BNC interfaces on the LMR-195 cable allow for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity SMA Plug Right Angle to Reverse Polarity BNC Plug Right Angle Low Loss Cable Using LMR-195 Coax PE3W10794](#)



Reverse Polarity SMA Plug Right Angle to Reverse Polarity
BNC Plug Right Angle Low Loss Cable Using LMR-195 Coax

RF Cable Assemblies Technical Data Sheet

PE3W10794

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		80		%
RF Shielding	90			dB
Group Delay		1.27 [4.17]		ns/ft [ns/m]
Capacitance		25.4 [83.33]		pF/ft [pF/m]
Inductance		0.064 [0.21]		uH/ft [uH/m]
DC Resistance Inner Conductor		7.6 [24.93]		Ω /1000ft [Ω /Km]
DC Resistance Outer Conductor		4.9 [16.08]		Ω /1000ft [Ω /Km]
Jacket Spark			3,000	Vrms

Mechanical Specifications

Cable Assembly

Weight 0.084 lbs [38.1 g]

Cable

Cable Type	LMR-195
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.195 in [4.95 mm]
One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	2 in [50.8 mm]
Bending Moment	0.2 lbs-ft [0.27 N-m]
Flat Plate Crush	15 lbs/in [0.27 Kg/mm]
Tensile Strength	40 lbs [18.14 Kg]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity SMA Plug Right Angle to Reverse Polarity BNC Plug Right Angle Low Loss Cable Using LMR-195 Coax PE3W10794](#)



Reverse Polarity SMA Plug Right Angle to Reverse Polarity
BNC Plug Right Angle Low Loss Cable Using LMR-195 Coax

RF Cable Assemblies Technical Data Sheet

PE3W10794

Connectors

Description	Connector 1	Connector 2
Type	SMA Plug Reverse Polarity Right Angle	BNC Plug Reverse Polarity Right Angle
Specification		MIL-C-39012
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Beryllium Copper, Gold	Brass, Gold
Contact Plating Specification		3 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification		70 µin minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification		70 µin minimum
Hex Size	5/16 in	
Torque	5 in-lbs [0.57 Nm]	

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity SMA Plug Right Angle to Reverse Polarity BNC Plug Right Angle Low Loss Cable Using LMR-195 Coax PE3W10794](#)



Reverse Polarity SMA Plug Right Angle to Reverse Polarity BNC Plug Right Angle Low Loss Cable Using LMR-195 Coax

RF Cable Assemblies Technical Data Sheet

PE3W10794

How to Order

Part Number Configuration:

PE3W10794

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W10794-12 = 12 inches long cable
PE3W10794-100cm = 100 cm long cable

Reverse Polarity SMA Plug Right Angle to Reverse Polarity BNC Plug Right Angle Low Loss Cable Using LMR-195 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity SMA Plug Right Angle to Reverse Polarity BNC Plug Right Angle Low Loss Cable Using LMR-195 Coax PE3W10794](https://www.pasternack.com/reverse-polarity-sma-plug-right-angle-to-reverse-polarity-bnc-plug-right-angle-low-loss-cable-using-lmr-195-pe3w10794-p.aspx)

URL: <https://www.pasternack.com/reverse-polarity-sma-plug-right-angle-to-reverse-polarity-bnc-plug-low-loss-cable-using-lmr-195-pe3w10794-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W10794 CAD Drawing

Reverse Polarity SMA Plug Right Angle to Reverse Polarity BNC
Plug Right Angle Low Loss Cable Using LMR-195 Coax

