

MMCX Plug to MCX Jack Bulkhead Cable Using RG188 Coax with HeatShrink




PE3W18778/HS

Configuration

- Connector 1: MMCX Plug
- Connector 2: MCX Jack Bulkhead
- Cable Type: RG188
- Coax Flex Type: Flexible

Features

- 70% Phase Velocity
- PTFE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W18778/HS MMCX plug to MCX jack bulkhead cable using RG188 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack MMCX to MCX cable assembly has a plug to jack gender configuration with 50 ohm flexible RG188 coax. Our RF cable assembly with MCX bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		70		%
Group Delay		1.45 [4.76]		ns/ft [ns/m]
DC Resistance Inner Conductor		84.1 [275.92]		Ohms/1000ft [Ohms/Km]

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.0122 lbs [5.53 g]

Cable

Cable Type	RG188
Impedance	50 Ohms

MMCX Plug to MCX Jack Bulkhead Cable Using RG188 Coax with HeatShrink



PE3W18778/HS

Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	PTFE, White
Jacket Diameter	0.11 in [2.79 mm]

Connectors

Description	Connector 1	Connector 2
Type	MMCX Plug	MCX Jack Bulkhead
Specification	BS EN 122340	CECC 22220
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold
Contact Plating Specification	30 µin minimum	50 µin minimum
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Gold	
Outer Conductor Plating Specification	3 µin minimum	
Body Material and Plating	Brass, Gold	Brass, Gold
Body Plating Specification	3 µin minimum	30 µin minimum

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

MMCX Plug to MCX Jack Bulkhead Cable Using RG188 Coax with HeatShrink



PE3W18778/HS

Typical Performance Data

How to Order

Part Number Configuration:

PE3W18778/HS

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length
Base Number

Example: PE3W18778/HS-12 = 12 inches long cable
PE3W18778/HS-100cm = 100 cm long cable

MMCX Plug to MCX Jack Bulkhead Cable Using RG188 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MMCX Plug to MCX Jack Bulkhead Cable Using RG188 Coax with HeatShrink PE3W18778/HS](https://www.pasternack.com/mmcx-plug-to-mcx-jack-bulkhead-cable-using-rg188-with-heatshrink-pe3w18778-hs-p.aspx)

URL: <https://www.pasternack.com/mmcx-plug-to-mcx-jack-bulkhead-cable-using-rg188-with-heatshrink-pe3w18778-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W18778/HS CAD Drawing

MMCX Plug to MCX Jack Bulkhead Cable Using RG188 Coax with HeatShrink

