

Slide-On BMA Jack 2 Hole Flange to MCX Jack Cable Using RG316 Coax with HeatShrink

PE3W20289/HS




Configuration

- Connector 1: Slide-On BMA Jack 2 Hole Flange
- Connector 2: MCX Jack
- Cable Type: RG316
- Coax Flex Type: Flexible

Features

- 69% Phase Velocity
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W20289/HS BMA jack slide-on 2 hole flange to MCX jack cable using RG316 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack BMA to MCX cable assembly has a jack to jack gender configuration with 50 ohm flexible RG316 coax. Our RF cable assembly with BMA 2 hole flange interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		69		%
Jacket Spark			2,000	Vrms

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.024 lbs [10.89 g]

Cable

Cable Type	RG316
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver

Slide-On BMA Jack 2 Hole Flange to MCX Jack Cable Using RG316 Coax with HeatShrink



PE3W20289/HS

Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.102 in [2.59 mm]

Connectors

Description	Connector 1	Connector 2
Type	BMA Jack 2 Hole Flange	MCX Jack
Specification		MIL-C-39012
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Connection Method	Slide-On	
Mating Cycles	1,000	
Contact Material and Plating	Beryllium Copper, Gold	Gold
Contact Plating Specification		MIL-G-45204
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Beryllium Copper, Gold	
Body Material and Plating	Brass, Tri-Metal	Brass, Nickel
Body Plating Specification		QQ-N-290

Environmental Specifications

Operating Range Temperature	-55 to +125 deg C
-----------------------------	-------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Slide-On BMA Jack 2 Hole Flange to MCX Jack Cable Using RG316 Coax with HeatShrink



PE3W20289/HS

Typical Performance Data

How to Order

Part Number Configuration:

PE3W20289/HS

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: PE3W20289/HS-12 = 12 inches long cable
PE3W20289/HS-100cm = 100 cm long cable

Slide-On BMA Jack 2 Hole Flange to MCX Jack Cable Using RG316 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Jack 2 Hole Flange to MCX Jack Cable Using RG316 Coax with HeatShrink PE3W20289/HS](https://www.pasternack.com/slide-on-bma-jack-2-hole-flange-to-mcx-jack-cable-using-rg316-with-heatshrink-pe3w20289-hs-p.aspx)

URL: <https://www.pasternack.com/slide-on-bma-jack-2-hole-flange-to-mcx-jack-cable-using-rg316-with-heatshrink-pe3w20289-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W20289/HS CAD Drawing

Slide-On BMA Jack 2 Hole Flange to MCX Jack Cable Using RG316 Coax with HeatShrink

