

Product Features

- Swivel Style
- 2400-2483 & 5150-5850 MHz Freq Range
- 7dBi Omni Radiation Pattern

Description

The PE51071 swivel style Rubber Duck Dual Band Antenna provides excellent performance in multiple wireless applications. Its small size and rugged construction is perfect for both indoor and portable wireless systems.

Specifications ⁽¹⁾

Parameter	Value	Units	Description
Band 1 Frequency	2400-2483	MHz	
Band 2 Frequency	5150-5850	MHz	
Impedance	50	Ohms	
Gain	7	dBi	
Polarization	Vertical		
RF Power Rating	30	W	Max
Maximum VSWR	<2.0	ratio	
Length	220	mm	8.66 inches
Connector Type		RP TNC Male	Swivel Style Reverse Polarity TNC



Ordering Information

Part Number	Description
PE51071	2400-2483 and 5150-5850 MHz 7dBi Dual Band Rubber Duck Antenna, Reverse Polarity TNC Male

(1) Pasternack reserves the right to change specifications or information without notice.

(2) All Specifications "Typical" values