

Product Features

- WiFi Rubber Duck Antenna
- 2300-2700 MHz Freq Range
- 2dBi Omni Radiation Pattern

Description

The PE51074 swivel style Rubber Duck Antenna provides excellent performance in multiple wireless applications. Its small size and rugged construction is perfect for both indoor and portable wireless systems.



Specifications ⁽¹⁾

| Parameter | Value | Units | Description |
|-----------------------|------------|-----------|------------------|
| Minimum Frequency | 2300 | MHz | |
| Maximum Frequency | 2700 | MHz | |
| Impedance | 50 | Ohms | |
| Gain | 2 | dBi | |
| Polarization | Vertical | | |
| RF Power Rating | 25 | W | Max |
| Maximum VSWR | <2.0 | ratio | |
| Length | 134 | mm | 5.28 inches |
| Connector Type | | RP-SMA(M) | Swivel Style SMA |
| Weight | 20 | grams | |
| Operating Temperature | -40 to +60 | Deg C | |

Ordering Information

| Part Number | Description |
|-------------|------------------------------------------------------------|
| PE51074 | 2300-2700 MHz Rubber Duck, 2dBi, Reverse Polarity-SMA Male |
| | |

(1) Pasternack reserves the right to change specifications or information without notice.

(2) All Specifications "Typical" values