

Antennas Technical Data Sheet

Features

- NMO Mount, Black Chrome Finish
- · One-piece 17-7 Stainless Steel open coil whip
- Flexible Black Polymer Alloy Spring

Applications

• Service Vehicles

· Public Safety

- Public Transportation
 - Mining & Construction

Description

This UHF mobile omnidirectional antenna is ideally suited for multipoint mobile applications including service vehicles, public transportation, public safety, mining and construction vehicles, as well numerous other commercial and industrial applications where mobility and wide coverage is desired. This antenna features a flexible Poly Spring base. Unlike the traditional metal spring base, the Poly Spring will not corrode and does not generate electrical noise when flexed during use. It has a standard TAD/NMO Motorola-type mobile base.

Configuration

J
Design
Application Band
Band Type
Radiation Pattern
Polarization
Ground Plane
Connector Type

Vehicular UHF Single **Omni Directional** Linear, Vertical Required NMO Mount

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range (Tunable Range)	420		470	MHz
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain		5		dB
Horizontal (Azimuth) Beam Width		Omnidirectional		
Vertical (Elevation) Beam Width		35		Degrees
Input Power			150	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 5 dB Tunable Poly Spring Vehicular Antenna 420-470 MHz NMO Mount Connector PE51MP1007

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



PE51MP1007

- · O-ring seal for waterproof construction
- Durable Xenoy[™] base with TPV over mold dust seal and grip ring



Antennas Technical Data Sheet

PE51MP1007

Mechanical Specifications

Base Material Whip Material Whip Finish Mounting Application Spring Material

Size Overall Length Xenoy™ w/TPV over mold grip 17-7 SS Black Chrome ¾ inch thru-hole NMO Mount Black Molded Polymer Alloy

38.39 in [975.11 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 5 dB Tunable Poly Spring Vehicular Antenna 420-470 MHz NMO Mount Connector PE51MP1007


Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

© 2019 Pasternack Enterprises All Rights Reserved



Antennas Technical Data Sheet

PE51MP1007



PE51MP1007

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com



Antennas Technical Data Sheet

PE51MP1007

WHIP CUTTING INSTRUCTIONS FOR TUNNING PE51MP1007 (420-470 MHz) PLEASE CAREFULLY READ ALL INSTRUCTIONS BEFORE CUTTING THE WHIP.

 IMPORTATN: Before Cutting. It is recommended to cut the whip longer than the required dimension to verify actual performance. Then trim the whip in 1/16" (1.5mm) increments to fine tune the desired VSWR response.


<u>CUTTING NOTE</u>: The whip can be cut using a grinding wheel or shearing tool designed for this purpose.

2. **Note:** Ensure the whip is located and completely seated inside the antenna whip adapter. The Tuned Length "W" is determined by measuring the distance between the top of the antenna adapter-spring and the bottom of the antenna phasing coil as shown in **Figure 4.** With the whip removed from the adapter, the cut length

FREQUENCY	TUNED WHIP LENGTH "W"		
(MHz)	(inches)	(mm)	
420.0	15-7/8	402	
425.0	15-1/4	387	
430.0	14-11/16	372	
435.0	14-1/16	357	
440.0	13-1/2	342	
445.0	13	329	
450.0	12-1/2	316	
455.0	12	304	
460.0	11-1/2	292	
465.0	11-1/16	281	
470.0	10-5/8	270	

Table 1

- dimension will be approximately 1" (25mm) longer than the Tuned Length "W".
- 3. Identify the desired center frequency of operation in the left column of TABLE 1. Imperial and Metric units are given for convenience.
- 4. <u>TUNING NOTE</u>: For frequencies not listed in TABLE 1, interpolation of Tuned Length "W" is permitted. When interpolating intermediate frequencies, the antenna frequency response increases by approximately 1 MHz for every 0.04" (1 mm) of cut length.
- 5. Cut the antenna whip as required to establish the specified Tuned Length "W" as shown in Figure 4.
- 6. Verify VSWR. Secure set screws (2 ea.).




[Note: Add 1" (25mm) to Tuned Length "W" when cutting whip.]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 5 dB Tunable Poly Spring Vehicular Antenna 420-470 MHz NMO Mount Connector PE51MP1007

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

© 2019 Pasternack Enterprises All Rights Reserved

PE51MP1007





Antennas Technical Data Sheet

PE51MP1007

5 dB Tunable Poly Spring Vehicular Antenna 420-470 MHz NMO Mount Connector from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 5 dB Tunable Poly Spring Vehicular Antenna 420-470 MHz NMO Mount Connector PE51MP1007

URL: https://www.pasternack.com/single-antenna-420-470-mhz-5-db-gain-nmo-mount-pe51mp1007-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE51MP1007 CAD Drawing

5 dB Tunable Poly Spring Vehicular Antenna 420-470 MHz NMO Mount Connector

