

## Fire Rated SMA Male to SMA Male Right Angle Low Loss Cable Using LMR-100-FR Coax with HeatShrink




### PE3W17015/HS

#### Configuration

- Connector 1: SMA Male
- Connector 2: SMA Male Right Angle
- Cable Type: LMR-100A-FR
- Coax Flex Type: Flexible

#### Features

- Max Frequency 6 GHz
- Shielding Effectivity > 90 dB
- 66% Phase Velocity
- Double Shielded
- FRPE Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3W17015/HS SMA male to SMA male right angle cable using LMR-100-FR coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to SMA cable assembly has a male to male gender configuration with 50 ohm flexible LMR-100A-FR coax. The PE3W17015/HS SMA male to SMA male cable assembly operates to 6 GHz. The right angle SMA interface on the LMR-100A-FR cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		66		%
RF Shielding	90			dB
Group Delay		1.54 [5.05]		ns/ft [ns/m]
Capacitance		30.8 [101.05]		pF/ft [pF/m]
Inductance		0.077 [0.25]		uH/ft [uH/m]
DC Resistance Inner Conductor		81 [265.75]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		9.5 [31.17]		Ohms/1000ft [Ohms/Km]

Fire Rated SMA Male to SMA Male Right Angle Low Loss Cable Using LMR-100-FR Coax with HeatShrink



**PE3W17015/HS**

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Jacket Spark			2,000	Vrms

**Specifications by Frequency**

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
			Frequency					MHz	
PE3W17015/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.115	0.165	0.24	0.398	0.641	dB/ft	
			0.38	0.55	0.79	1.31	2.11	dB/m	
PE3W17015/HS-24	24 In	Insertion Loss (Typ.)	0.53	0.63	0.78	1.1	1.59	dB	0.047
PE3W17015/HS-36	36 In	Insertion Loss (Typ.)	0.65	0.8	1.02	1.5	2.23	dB	0.056
PE3W17015/HS-48	48 In	Insertion Loss (Typ.)	0.76	0.96	1.26	1.9	2.87	dB	0.065
PE3W17015/HS-100CM	100 CM	Insertion Loss (Typ.)	0.68	0.85	1.09	1.61	2.41	dB	0.059
PE3W17015/HS-200CM	200 CM	Insertion Loss (Typ.)	1.06	1.39	1.88	2.92	4.51	dB	0.089

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.2 dB
Base Weight:	0.038 pounds
Additional Weight per Inch:	0.00075 pounds

**Mechanical Specifications**

**Cable Assembly**

Width/Diameter	0.5 in [12.7 mm]
Weight	0.029 lbs [13.15 g]

**Cable**

Cable Type	LMR-100A-FR
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper
Jacket Material	FRPE, Black
Jacket Diameter	0.11 in [2.79 mm]
One Time Minimum Bend Radius	0.25 in [6.35 mm]
Repeated Minimum Bend Radius	1 in [25.4 mm]
Bending Moment	0.1 lbs-ft [0.14 N-m]
Flat Plate Crush	10 lbs/in [0.18 Kg/mm]
Tensile Strength	15 lbs [6.8 Kg]

Fire Rated SMA Male to SMA Male Right Angle Low Loss Cable Using LMR-100-FR Coax with HeatShrink



**PE3W17015/HS**

**Connectors**

Description	Connector 1	Connector 2
Type	SMA Male	SMA Male Right Angle
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 µin minimum	50 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin minimum	100 µin minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	100 µin minimum	100 µin minimum
Hex Size	5/16 inch	5/16 inch
Torque	3 in-lbs 0.34 Nm	3 in-lbs 0.34 Nm

**Environmental Specifications**

Operating Range Temperature -40 to +85 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:


Fire Rated SMA Male to SMA Male Right Angle Low Loss Cable Using LMR-100-FR Coax with HeatShrink



**PE3W17015/HS**

**Typical Performance Data**

**How to Order**



Example: PE3W17015/HS-12 = 12 inches long cable  
PE3W17015/HS-100cm = 100 cm long cable

Fire Rated SMA Male to SMA Male Right Angle Low Loss Cable Using LMR-100-FR Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Fire Rated SMA Male to SMA Male Right Angle Low Loss Cable Using LMR-100-FR Coax with HeatShrink PE3W17015/HS](https://www.pasternack.com/fire-rated-sma-male-to-sma-male-right-angle-low-loss-cable-using-lmr-100-fr-coax-with-heatshrink-pe3w17015-hs)

URL: <https://www.pasternack.com/fire-rated-sma-male-to-sma-male-low-loss-cable-using-lmr-100-fr-with-heatshrink-pe3w17015-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE3W17015/HS CAD Drawing

Fire Rated SMA Male to SMA Male Right Angle Low Loss Cable Using LMR-100-FR Coax with HeatShrink



REVISION		DATE	CHANGED BY	APPROVED
ZONE	REV			
	A	11/18/2024	TDOFRENE	AGANWANI
DESCRIPTION				
INITIAL RELEASE				

<b>PASTERNAK</b> an INFINITE brand		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE NONE SHEET 1 OF 1
Website: <a href="http://www.Pasternack.com">www.Pasternack.com</a> Phone: 1.866.727.8376   1.949.261.1920		
DESCRIPTION <b>SMA MALE TO SMA MALE RIGHT ANGLE LOW LOSS CABLE USING LMR-100-FR COAX WITH HEATSHRINK</b>		
SIZE A	CAGE CODE 53919	ITEM NO. PE3W17015/HS
DRAWN BY KGLEBOVA		REV A

**UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE IN INCHES DIMENSIONS IN [ ] ARE MILLIMETERS**

**TOLERANCES:**  
 .X = ±.2 [5]  
 .XX = ±.02 [0.5]  
 .XXX = ±.005 [0.13]

**FRACTIONS**  
 ± 1/32  
 ANGLES ± 1°

**CABLE LENGTH TOLERANCES:**  
 ≤ 12 [305] ± .60 [15.24] = +.1 [2.5] / -0  
 > 12 [305] ≤ 60 [1524] = +.4 [10.27] / -0  
 > 60 [1524] ≤ 120 [3048] = +.4 [10.27] / -0  
 > 120 [3048] ≤ 300 [7620] = +.5% / -0

**ALL DIMENSIONS ARE FOR REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE NON-CRITICAL FEATURES. DIMENSIONS MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.**

**NOTES:**

- CABLE ASSY LENGTH LABEL PLACEMENT: .36 INCHES OR LESS. ONE LABEL APPROX CENTERED. LONGER THAN .36 INCHES. TWO LABELS APPROX 6 INCHES FROM EACH CONNECTOR.
- CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.
- CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

PE DS Rev-D4-A326