

SMA Female to TNC Male Cable Using RG142 Coax




PE3W17237

Configuration

- Connector 1: SMA Female
- Connector 2: TNC Male
- Cable Type: RG142
- Coax Flex Type: Flexible

Features

- Shielding Effectivity > 70 dB
- 70% Phase Velocity
- Double Shielded
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W17237 SMA female to TNC male cable using RG142 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to TNC cable assembly has a female to male gender configuration with 50 ohm flexible RG142 coax. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 70 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		70		%
RF Shielding	70			dB
Capacitance		96.45 [316.44]		pF/ft [pF/m]
DC Resistance Inner Conductor		65 [213.25]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		9 [29.53]		Ohms/1000ft [Ohms/Km]

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.084 lbs [38.1 g]

Cable

Cable Type	RG142
------------	-------

SMA Female to TNC Male Cable Using RG142 Coax



PE3W17237

Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.195 in [4.95 mm]
One Time Minimum Bend Radius	0.98 in [24.89 mm]
Repeated Minimum Bend Radius	1.97 in [50.04 mm]

Connectors

Description	Connector 1	Connector 2
Type	SMA Female	TNC Male
Specification	MIL-STD-348	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Gold	Brass, Gold
Contact Plating Specification	MIL-G-45204	30 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	QQ-N-290	100 μ in minimum
Coupling Nut Material and Plating		Brass, Nickel
Coupling Nut Plating Specification		100 μ in minimum

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

SMA Female to TNC Male Cable Using RG142 Coax

**PE3W17237****Typical Performance Data****How to Order**

Part Number Configuration:

PE3W17237	- xx	uu	
			Unit of Measure:
			cm = Centimeters
			<blank> = Inches
			Length
			Base Number

Example: PE3W17237-12 = 12 inches long cable
PE3W17237-100cm = 100 cm long cable

SMA Female to TNC Male Cable Using RG142 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female to TNC Male Cable Using RG142 Coax PE3W17237](#)

URL: <https://www.pasternack.com/sma-female-to-tnc-male-cable-using-rg142-pe3w17237-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W17237 CAD Drawing

SMA Female to TNC Male Cable Using RG142 Coax

