

Reverse Polarity TNC Plug to SMA Male Right Angle Low Loss Cable Using LMR-240 Coax with HeatShrink




PE3W18628/HS

Configuration

- Connector 1: TNC Plug Reverse Polarity
- Connector 2: SMA Male Right Angle
- Cable Type: LMR-240
- Coax Flex Type: Flexible

Features

- Max Frequency 6 GHz
- Shielding Effectivity > 90 dB
- 84% Phase Velocity
- Double Shielded
- PE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W18628/HS reverse polarity TNC plug to SMA male right angle cable using LMR-240 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack reverse polarity TNC to SMA cable assembly has a plug to male gender configuration with 50 ohm flexible LMR-240 coax. The PE3W18628/HS reverse polarity TNC plug to SMA male cable assembly operates to 6 GHz. The right angle SMA interface on the LMR-240 cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		84		%
RF Shielding	90			dB
Group Delay		1.21 [3.97]		ns/ft [ns/m]
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		3.2 [10.5]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		3.89 [12.76]		Ohms/1000ft [Ohms/Km]

Reverse Polarity TNC Plug to SMA Male Right Angle Low Loss Cable Using LMR-240 Coax with HeatShrink



PE3W18628/HS

Electrical Specifications

Description	Minimum	Typical				Maximum	Units
Jacket Spark					5,000		Vrms

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	250	500	1000	2500	6000	MHz	
PE3W18628/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.039	0.056	0.076	0.129	0.204	dB/ft	
			0.13	0.19	0.25	0.43	0.67	dB/m	
PE3W18628/HS-12	12 inch	Insertion Loss (Typ.)	0.39	0.41	0.43	0.48	0.56	dB	0.154
PE3W18628/HS-24	24 inch	Insertion Loss (Typ.)	0.43	0.47	0.51	0.61	0.76	dB	0.187
PE3W18628/HS-36	36 inch	Insertion Loss (Typ.)	0.47	0.52	0.58	0.74	0.97	dB	0.22
PE3W18628/HS-48	48 inch	Insertion Loss (Typ.)	0.51	0.58	0.66	0.87	1.17	dB	0.253
PE3W18628/HS-60	60 inch	Insertion Loss (Typ.)	0.55	0.63	0.73	1	1.37	dB	0.286

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB
Loss due to Connector 2: 0.25 dB
Base Weight: 0.154 pounds
Additional Weight per Inch: 0.00275 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter 0.5 in [12.7 mm]
Weight 0.154 lbs [69.85 g]

Cable

Cable Type LMR-240
Impedance 50 Ohms
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper
Dielectric Type PE (F)
Number of Shields 2
Shield Layer 1 Aluminum Tape
Shield Layer 2 Tinned Copper Braid
Jacket Material PE, Black
Jacket Diameter 0.24 in [6.1 mm]
One Time Minimum Bend Radius 0.75 in [19.05 mm]
Repeated Minimum Bend Radius 2.5 in [63.5 mm]
Bending Moment 0.25 lbs-ft [0.34 N-m]
Flat Plate Crush 20 lbs/in [0.36 Kg/mm]
Tensile Strength 80 lbs [36.29 Kg]

Reverse Polarity TNC Plug to SMA Male Right Angle Low Loss Cable Using LMR-240 Coax with HeatShrink



PE3W18628/HS

Connectors

Description	Connector 1	Connector 2
Type	TNC Plug Reverse Polarity	SMA Male Right Angle
Specification	MIL-STD-348	MIL-STD-348
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Mating Cycles		500
Contact Material and Plating	Beryllium Copper, Gold over nickel	Brass/Phosphor Bronze, Gold
Contact Plating Specification		50 μ inch
Dielectric Type	PTFE	Teflon
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification		80 μ inch
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Plating Specification		80 μ inch
Hex Size		5/16 Inch
Torque		7 in-lbs 0.79 Nm

Environmental Specifications

Operating Range Temperature -40 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Reverse Polarity TNC Plug to SMA Male Right Angle Low Loss Cable Using LMR-240 Coax with HeatShrink




PE3W18628/HS

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3W18628/HS-12 = 12 inches long cable
PE3W18628/HS-100cm = 100 cm long cable

Reverse Polarity TNC Plug to SMA Male Right Angle Low Loss Cable Using LMR-240 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity TNC Plug to SMA Male Right Angle Low Loss Cable Using LMR-240 Coax with HeatShrink PE3W18628/HS](#)

URL: <https://www.pasternack.com/reverse-polarity-tnc-plug-to-sma-male-low-loss-cable-using-lmr-240-with-heatshrink-pe3w18628-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W18628/HS CAD Drawing

Reverse Polarity TNC Plug to SMA Male Right Angle Low Loss Cable Using LMR-240 Coax with HeatShrink

