

0 to 41 dB Push Button Step Attenuator, N Female to N Female with 1 dB Step Rated to 5 Watts Up to 4 GHz



PE70A1050N

Features

- 1, 2, 4, 8, 10, and 16 dB step buttons
- 0 to 41 dB Attenuation
- 1.55:1 VSWR Maximum
- 1.8 dB Attenuation Accuracy Maximum
- N-Type Female Connectors
- Maximum Power 5 Watts (CW)

Applications

- Instrumentation
- Precision Measurements
- Prototyping and Characterization
- Production Systems

Description

The PE70A1050N is a Step Attenuator that has 41 dB of total attenuation with 1, 2, 4, 8, 10, and 16 dB push button steps, designed across the frequency range of DC to 4 GHz. Select button for desired attenuation level, total attenuation is the sum of all buttons selected. The design is tried and true technology that offers exceptional performance characteristics that include 4.5 dB maximum insertion loss, and a maximum VSWR of 1.55:1. The design also features excellent attenuation accuracy with 1.8 dB maximum. The Aluminum package has N-Type Female connectors, and operates within the temperature range of -20°C to 85°C.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|--------------------------------|---------|-------------|---------|-------|
| Frequency Range | DC | | 4 | GHz |
| Impedance | | 50 | | Ohms |
| Insertion Loss | | | 4.5 | dB |
| Attenuation Value | | 0 to 41 | | dB |
| Step Size | | 1 | | dB |
| Step Type | | Push Button | | |
| Accuracy Statement | | ±1.8 dB | | |
| Input Power (CW) | | | 5 | Watts |
| Input Power, Peak | | | 100 | Watts |
| 5 µs pulse width 2% duty cycle | | | | |
| VSWR | | | 1.55:1 | |

Mechanical Specifications

Size

| | |
|---------------------------|---------------------|
| Length | 5.28 in [134.11 mm] |
| Width | 1.4 in [35.56 mm] |
| Height | 0.79 in [20.07 mm] |
| Weight | 0.31 lbs [140.61 g] |
| Body Material and Plating | Aluminum, Paint |

Connectors

| Description | Connector 1 | Connector 2 |
|-------------|-------------|-------------|
| Type | N Female | N Female |

0 to 41 dB Push Button Step Attenuator, N Female to N Female with 1 dB Step Rated to 5 Watts Up to 4 GHz



PE70A1050N

Connectors

| Description | Connector 1 | Connector 2 |
|------------------------------|------------------------|------------------------|
| Contact Material and Plating | Beryllium Copper, Gold | Beryllium Copper, Gold |
| Body Material and Plating | Brass, Nickel | Brass, Nickel |

Environmental Specifications

Temperature

Operating Range

-20 to 85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

0 to 41 dB Push Button Step Attenuator, N Female to N Female with 1 dB Step Rated to 5 Watts Up to 4 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [0 to 41 dB Push Button Step Attenuator, N Female to N Female with 1 dB Step Rated to 5 Watts Up to 4 GHz PE70A1050N](#)

URL: <https://www.pasternack.com/41db-step-n-female-n-female-5-watts-attenuator-pe70a1050n-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE70A1050N CAD Drawing

0 to 41 dB Push Button Step Attenuator, N Female to N Female with 1 dB Step Rated to 5 Watts Up to 4 GHz

