

SMA Male to SMA Male Cable Using TCOM-400 Coax with HeatShrink




PE3W19360/HS

Configuration

- Connector 1: SMA Male
- Connector 2: SMA Male
- Cable Type: TCOM-400
- Coax Flex Type: Flexible

Features

- Max Frequency 10 GHz
- Shielding Effectivity > 100 dB
- 85% Phase Velocity
- Double Shielded
- PE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W19360/HS SMA male to SMA male cable using TCOM-400 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to SMA cable assembly has a male to male gender configuration with 50 ohm flexible TCOM-400 coax. The PE3W19360/HS SMA male to SMA male cable assembly operates to 10 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 100 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		10	GHz
VSWR			1.4:1	
Velocity of Propagation		85		%
RF Shielding	100			dB
Group Delay		1.2 [3.94]		ns/ft [ns/m]
Capacitance		23.9 [78.41]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		1.39 [4.56]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		1.47 [4.82]		Ohms/1000ft [Ohms/Km]

SMA Male to SMA Male Cable Using TCOM-400 Coax with HeatShrink



PE3W19360/HS

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Jacket Spark			8,000	Vrms

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
			Frequency					MHz	
PE3W19360/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.03	0.044	0.072	0.104	0.157	dB/ft	
			0.1	0.15	0.24	0.35	0.52	dB/m	
PE3W19360/HS-6	6 inch	Insertion Loss (Typ.)	0.22	0.23	0.24	0.26	0.28	dB	0.18
PE3W19360/HS-9	9 inch	Insertion Loss (Typ.)	0.23	0.24	0.26	0.28	0.32	dB	0.2
PE3W19360/HS-12	12 inch	Insertion Loss (Typ.)	0.23	0.25	0.28	0.31	0.36	dB	0.22
PE3W19360/HS-18	18 inch	Insertion Loss (Typ.)	0.25	0.27	0.31	0.36	0.44	dB	0.26
PE3W19360/HS-24	24 inch	Insertion Loss (Typ.)	0.26	0.29	0.35	0.41	0.52	dB	0.3

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.1 dB
Base Weight:	0.22 pounds
Additional Weight per Inch:	0.0066 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.705 in [17.91 mm]
Weight	0.22 lbs [99.79 g]

Cable

Cable Type	TCOM-400
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Aluminum
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.405 in [10.29 mm]
One Time Minimum Bend Radius	1 in [25.4 mm]
Repeated Minimum Bend Radius	4 in [101.6 mm]
Bending Moment	0.5 lbs-ft [0.68 N-m]
Flat Plate Crush	40 lbs/in [0.71 Kg/mm]
Tensile Strength	160 lbs [72.57 Kg]

SMA Male to SMA Male Cable Using
TCOM-400 Coax with HeatShrink



PE3W19360/HS

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SMA Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Gold	Brass, Gold
Coupling Nut Material and Plating	Brass, Gold	Brass, Gold
Hex Size	5/16 inch	5/16 inch
Torque	3 in-lbs 0.34 Nm	3 in-lbs 0.34 Nm

Environmental Specifications

Operating Range Temperature -40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

SMA Male to SMA Male Cable Using TCOM-400 Coax with HeatShrink




PE3W19360/HS

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3W19360/HS-12 = 12 inches long cable
PE3W19360/HS-100cm = 100 cm long cable

SMA Male to SMA Male Cable Using TCOM-400 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Cable Using TCOM-400 Coax with HeatShrink PE3W19360/HS](#)

URL: <https://www.pasternack.com/sma-male-to-sma-male-cable-using-tcom-400-with-heatshrink-pe3w19360-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W19360/HS CAD Drawing

SMA Male to SMA Male Cable Using TCOM-400 Coax with HeatShrink



NOTES:

1. CABLE ASSY LENGTH LABEL PLACEMENT: 36 INCH OR LESS, ONE LABEL APPROXIMATELY CENTERED, LONGER THAN 36 INCH, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.
3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVISION CONTRARY TO U.S. LAW PROHIBITED.

PE DS Rev-04 Add2

REVISION		DATE	CHANGED BY	APPROVED
ZONE	REV			
	A	02/13/2026	AKRESOWSKI	DWANG
DESCRIPTION				
INITIAL RELEASE				

		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
Website: www.Pasternack.com Phone: 1.866.727.8376 1.949.261.1920		SCALE	SHEET
		NONE	1 OF 1
SMA MALE TO SMA MALE CABLE USING TCOM-400 COAX WITH HEATSHRINK			
DESCRIPTION	SIZE	CAGE CODE	ITEM NO.
	A	53919	PE3W19360/HS
DRAWN BY		REV	
AKRESOWSKI		A	

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. DIMENSIONS IN PARENTHESES ARE IN MILLIMETERS.

TOLERANCES:

X = ±.2 (5) FRACTIONS ± 1/32

.XX = ±.02 (0.5) ANGLES ± 1°

.XXX = ±.005 (0.13)

CABLE LENGTH TOLERANCES:

>12 (305) ≤ 60 (1524) = +.1 (25) / -0

>60 (1524) ≤ 120 (3048) = +.4 (102) / -0

>120 (3048) ≤ 300 (7620) = +.5 (12.7) / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY. DIMENSIONS OF NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.