



SPDT Electromechanical Relay Pulse Latching
 Switch DC to 18 GHz, SMA, 35 Watts,
 175V Indicator, 12V Control with Indicators

Electromechanical Relay Switches Technical Data Sheet

PE7146

Features

- SPDT Switch
- DC to 18GHz Frequency Range
- 1M Cycles Min Lifetime
- Pulse Latching Switch
- Break before Make
- -40 to +85 Deg C Operating Temperature
- Insertion Loss 0.5 dB Max
- VSWR 1.5:1 Max
- +12 Vdc Operating Voltage

Applications

- Test & Measurement
- Instrumentation

Description

The PE7146 is a Single Pole Double Throw Electromechanical Relay Switch that operates from DC to 18 GHz and can handle up to 85 Watts of CW input power in a Break before Make condition. This design features a Pulse Latching Actuator with Indicators and is rated for 1M Life Cycles. Insertion loss is specified from 0.2 dB max and Isolation from 80 dB min, with +8.5 Vdc operating voltage. Performance is guaranteed over -40 deg C to +85 deg C, and the switch assembly is RoHS and REACH compliant. The package interface uses solder terminals and SMA female connectors.

Electrical Specifications

Switch Type	SPDT, Reflective
Actuator Type	Pulse Latching
Switching Sequence	Break before Make
Actuator Options	Indicators
Pickup Voltage	8.5 Volts
Indicator Rating	5 Watts / 175 Volts / 250 mA

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
Impedance		50		Ohms
Operating Voltage	10	12	14	Volts
Actuating Current @ 12 Volts			215	mA
VSWR			1.5:1	
Insertion Loss			0.5	dB
Isolation	60			dB
Input Power (CW)			35	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SPDT Electromechanical Relay Pulse Latching Switch DC to 18 GHz, SMA, 35 Watts, 175V Indicator, 12V Control with Indicators PE7146](#)



SPDT Electromechanical Relay Pulse Latching
 Switch DC to 18 GHz, SMA, 35 Watts,
 175V Indicator, 12V Control with Indicators

Electromechanical Relay Switches Technical Data

PE7146

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 4	4 to 8	8 to 12.4	12.4 to 18		GHz
VSWR, Max	1.2:1	1.3:1	1.4:1	1.5:1		
Insertion Loss, Max	0.2	0.3	0.4	0.5		dB
Isolation, Min	80	70	60	60		dB
Input Power, Typ (CW)	85	55	45	35		Watts

Electrical Specification Notes:

Recommended pulse width duration for switching relay, 50-500 milliseconds

Mechanical Specifications

Size

Length	1.34 in [34.04 mm]
Width/Diameter	0.5 in [12.7 mm]
Height	2.13 in [54.1 mm]
Weight	0.088 lbs [39.92 g]
Body Material and Plating	Aluminum, Black Anodized
Package Type	Connectorized Module
Operating Life	1,000,000 Cycles
Switching Time	15 ms Max

Connectors

RF Connector Type	SMA Female
RF Connector Contact Material and Plating	Beryllium Copper, Gold
RF Connector Body Material and Plating	Passivated Stainless Steel
Control Connector	Solder Terminals

Mechanical Specification Notes:

RF Connector mating requirements per MIL-C-39012

Environmental Specifications

Temperature

Operating Range	-40 to +85 deg C
Storage Range	-55 to +100 deg C

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant	
REACH Compliant	12/17/2014

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SPDT Electromechanical Relay Pulse Latching Switch DC to 18 GHz, SMA, 35 Watts, 175V Indicator, 12V Control with Indicators PE7146](#)





SPDT Electromechanical Relay Pulse Latching
Switch DC to 18 GHz, SMA, 35 Watts,
175V Indicator, 12V Control with Indicators

Electromechanical Relay Switches Technical Data

PE7146

Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SPDT Electromechanical Relay Pulse Latching Switch DC to 18 GHz, SMA, 35 Watts, 175V Indicator, 12V Control with Indicators PE7146](#)



SPDT Electromechanical Relay Pulse Latching
Switch DC to 18 GHz, SMA, 35 Watts,
175V Indicator, 12V Control with Indicators

Electromechanical Relay Switches Technical Data

PE7146

SPDT Electromechanical Relay Pulse Latching Switch DC to 18 GHz, SMA, 35 Watts, 175V Indicator, 12V Control with Indicators from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SPDT Electromechanical Relay Pulse Latching Switch DC to 18 GHz, SMA, 35 Watts, 175V Indicator, 12V Control with Indicators PE7146](#)

URL: <http://www.pasternack.com/sma-relay-switch-pe7146-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE7146 CAD Drawing

SPDT Electromechanical Relay Pulse Latching Switch DC to 18 GHz,
SMA, 35 Watts, 175V Indicator, 12V Control with Indicators



NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES (mm).

DWG TITLE
PE7146

FSCM NO. 53919

CAD FILE 090815

SCALE N/A

SIZE A


150

PE PASTERNAK
THE ENGINEER'S RF SOURCE

Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

PE7146 CAD Drawing

SPDT Electromechanical Relay Pulse Latching Switch DC to 18 GHz,
SMA, 35 Watts, 175V Indicator, 12V Control with Indicators



DWG TITLE

PE7146

- NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].

FSCM NO. 53919

CAD FILE 090815

SCALE N/A

SIZE A

150



Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com