



SMA RF Relay DPDT Switch From DC To 18 GHz Rated To 35 Watts And 24 Volts To 32 Volts With I, P, T, TTL Features

TECHNICAL DATA SHEET

PE7157

SMA RF Relay DPDT Switch From DC To 18 GHz Rated To 35 Watts And 24 Volts To 32 Volts With I, P, T, TTL Features

Configuration

RF Connector	SMA Female
RF Connector Specification	MIL-C-39012
Control Connector	Solder Terminals
Frequency Range, GHz	DC to 18
Design	DPDT

Electrical Specifications

Frequency Range, GHz	DC to 18
Impedance, Ohms	50
Maximum Input Power, Watts	35
Maximum Input VSWR	1.5:1
Maximum Insertion Loss, dB	0.5
Minimum Isolation, dB	60
Maximum Speed, ms	15
Control Voltage, Volts	24
Actuating Current, mA	175
Indicator Voltage, Volts	32

Frequency 1

Range, GHz	DC to 4
Insertion Loss, dB	0.2
VSWR	1.2
Maximum Input Power, Watts	85
Minimum Isolation, dB	80

Frequency 2

Range, GHz	4 to 8
Insertion Loss, dB	0.3
VSWR	1.3:1
Maximum Input Power, Watts	55
Minimum Isolation, dB	70

Frequency 3

Range, GHz	8 to 12.4
Insertion Loss, dB	0.4
VSWR	1.4:1
Maximum Input Power, Watts	45
Minimum Isolation, dB	60

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA RF Relay DPDT Switch From DC To 18 GHz Rated To 35 Watts And 24 Volts To 32 Volts With I, P, T, TTL Features PE7157](#)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.



SMA RF Relay DPDT Switch From DC To 18 GHz Rated To 35 Watts And 24 Volts To 32 Volts With I, P, T, TTL Features

TECHNICAL DATA SHEET

PE7157

Frequency 4

Range, GHz	12.4 to 18
Insertion Loss, dB	0.5
VSWR	1.5:1
Maximum Input Power, Watts	35
Minimum Isolation, dB	60

Mechanical Specifications

Temperature

Operating Range, deg C	-40 to +85
Storage Range, deg C	-55 to +100

Size

Length, in [mm]	2.25 [57.15]
Width, in [mm]	2.38 [60.45]
Height, in [mm]	0.52 [13.21]
Weight, lbs [g]	0.16 [72.57]
Housing Material and Plating	Aluminum, Black Anodized

RF Connector

Contact Material and Plating	Beryllium Copper, Gold
Body Material and Plating	Passivated Stainless Steel

Control Connector

Contact Material and Plating	Iron Nickel, Tin
------------------------------	------------------

Compliance Certifications (visit www.Pasternack.com for current document)

Plotted and Other Data

Notes:	Values at 25 °C, sea level
--------	----------------------------

SMA RF Relay DPDT Switch From DC To 18 GHz Rated To 35 Watts And 24 Volts To 32 Volts With I, P, T, TTL Features from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA RF Relay DPDT Switch From DC To 18 GHz Rated To 35 Watts And 24 Volts To 32 Volts With I, P, T, TTL Features PE7157](http://www.pasternack.com/sma-electromechanical-dpdt-switch-18ghz-35watts-24-32volts-i-p-t-ttl-pe7157-p.aspx)

URL: <http://www.pasternack.com/sma-electromechanical-dpdt-switch-18ghz-35watts-24-32volts-i-p-t-ttl-pe7157-p.aspx>


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

PE7157 CAD Drawing

SMA RF Relay DPDT Switch From DC To 18 GHz Rated To 35 Watts
And 24 Volts To 32 Volts With I, P, T, TTL Features



SCHEMATIC SHOWN IN POSITION 1
(+1 LAST ENERGIZED)



DWG TITLE

PE7157

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

PASTERNAK®
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623

Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

FSCM NO. 53919

CAD FILE 030309-A

SCALE N/A

SIZE A

XXXX