



Absorptive SPDT PIN Diode Switch Operating From
2 GHz to 40 GHz Up to +27 dBm and 2.92mm

PIN Diode Switches Technical Data Sheet

PE71S2022

Features

- SPDT Absorptive Switch
- 2 GHz to 40 GHz
- Insertion Loss 5.5 dB max
- Isolation 55 dB min
- Power Input +27 dBm CW max

Applications

- Test & Measurement
- Military Communication
- Commercial Communication

Description

The PE71S2022 is a SINGLE POLE DOUBLE THROW (SPDT) ABSORPTIVE PIN DIODE SWITCH that operates from 2 to 40 GHz. J1 and J2 ports are terminated in 50 ohms when switched in the isolation (off) state. Electrical performance includes 5.5 dB max insertion loss, -5 dB max return loss, 55 dB min isolation, and 100 nsec max switching speed. The design incorporates TTL-compatible driver circuitry for accurate logic control. Operational temperature range is -30°C to +60°C and dual voltage controls of +5 Vdc and -5 Vdc are required. The package interface uses solder terminals and 2.92mm Female connectors.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	2		40	GHz
Impedance		50		Ohms
Return Loss			-5	dB
Insertion Loss			5.5	dB
Isolation	55			dB
Switching Time			100	ns
Input Power (CW)			0.5	Watts
Positive Operating Voltage		5		Vdc
Negative Operating Voltage		-5		Vdc
Operating Temperature	-30		+60	deg C

Electrical Specification Notes:
Specified switching time includes TTL driver delay.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Absorptive SPDT PIN Diode Switch Operating From 2 GHz to 40 GHz Up to +27 dBm and 2.92mm PE71S2022](#)



Absorptive SPDT PIN Diode Switch Operating From
2 GHz to 40 GHz Up to +27 dBm and 2.92mm

PIN Diode Switches Technical Data Sheet

PE71S2022

Mechanical Specifications

Size

Length	1 in [25.4 mm]
Width	1.2 in [30.48 mm]
Height	0.6 in [15.24 mm]
Weight	0.119 lbs [53.98 g]
Design	Absorptive, SPDT
RF Connector	2.92mm Female
TTL Control Connector	2.92mm Female

Environmental Specifications

Temperature

Operating Range	-30 to +60 deg C
ESD Sensitivity	ESD Sensitive Material. Transport material in Approved ESD bags. Handle only in ESD Workstation.



Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Absorptive SPDT PIN Diode Switch Operating From 2 GHz to 40 GHz Up to +27 dBm and 2.92mm PE71S2022](#)





Absorptive SPDT PIN Diode Switch Operating From
2 GHz to 40 GHz Up to +27 dBm and 2.92mm

PIN Diode Switches Technical Data Sheet

PE71S2022

Typical Performance Data




Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Absorptive SPDT PIN Diode Switch Operating From 2 GHz to 40 GHz Up to +27 dBm and 2.92mm PE71S2022](#)



Absorptive SPDT PIN Diode Switch Operating From
2 GHz to 40 GHz Up to +27 dBm and 2.92mm

PIN Diode Switches Technical Data Sheet

PE71S2022



Absorptive SPDT PIN Diode Switch Operating From 2 GHz to 40 GHz Up to +27 dBm and 2.92mm from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Absorptive SPDT PIN Diode Switch Operating From 2 GHz to 40 GHz Up to +27 dBm and 2.92mm PE71S2022](https://www.pasternack.com/absorptive-spdt-pin-diode-switch-40-ghz-27-dbm-2.92mm-pe71s2022-p.aspx)

URL: <https://www.pasternack.com/absorptive-spdt-pin-diode-switch-40-ghz-27-dbm-2.92mm-pe71s2022-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE71S2022 CAD Drawing

Absorptive SPDT PIN Diode Switch Operating From 2 GHz
to 40 GHz Up to +27 dBm and 2.92mm



UNLESS OTHERWISE SPECIFIED:

DIMENSIONS ARE IN: inches

TOLERANCES ARE: [mm]

.XX ±.01 [±.25]

.XXX ±.001 [±.025]

* THESE DIMENSIONS AND TOLERANCES
SUPERSEDE NOTE #1 ON TITLE BLOCK.

LOGIC TABLE		
TTL	LOW	ISOLATION
LOGIC	LOSS	
HIGH	C-J2	C-J1
LOW	C-J1	C-J2

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].
4. FITS MIL-C-17 AND EQUIVALENT CABLES.

DWG TITLE

PE71S2022

PE PASTERNAK®
THE ENGINEER'S RF SOURCE

Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

FSCM NO. 53919

CAD FILE 102615

SCALE N/A

SIZE A

2233