



# **Electromechanical Relay Switches Technical Data Sheet**

PE71S6071

### **Features**

- · Transfer Relay Switch
- DC to 40 GHz Frequency Range
- 2.5M Cycle Min Operating Life
- 10 Watt Avg Power Max

- -40 to +85 Deg C Operating Temperature
- Insertion Loss 0.8 dB Max
- VSWR 1.9:1 Max

## **Applications**

- High Performance Relay Switch
- Military Communications
- · Communications Systems
- Test & Measurement

### **Description**

The PE71S6071 is a Transfer Electromechanical Relay Switch that operates from DC to 40 GHz and can handle up to 80 Watts of CW input power in a Break Before Make condition. The design features a Latching Actuator with Position Indicators and Self Cut Off circuitry and is rated for 2.5M Life Cycles for high reliability operation. Insertion loss is specified from 0.3 dB max and Isolation from 70 dB min, with +28 Vdc operating voltage. Performance is guaranteed over -40°C to +85°C and the switch assembly is RoHS and REACH compliant. The package interface uses solder terminals and 2.92mm Female connectors.

### **Electrical Specifications**

Switch Type
Actuator Type
Switching Sequence
Actuator Options
Polarity
Indicator Rating
Self Cut-Off Time

Transfer, Reflective
Latching
Break before Make
Indicators, Self Cut Off
Negative Common
1 Watts / 30 Volts / 100 mA
40 ms < CT < 120 ms

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		40	GHz
Impedance		50		Ohms
Operating Voltage	24	28	30	Volts
Actuating Current @ 28 Volts		125		mA
VSWR			1.9:1	
Insertion Loss			0.8	dB
Isolation	50			dB
Input Power (CW)			10	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Transfer Electromechanical Relay Latching Switch DC to 40 GHz, 2.92mm, 10 Watts, 30V Indicator, 28V Control with Indicators, Self Cut Off PE71S6071

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





# **Electromechanical Relay Switches Technical Data**

PE71S6071

#### Performance by Frequency

F1	F2	F3	F4	F5	Units
DC to 6	6 to 12.4	12.4 to 18	18 to 26.5	26.5 to 40	GHz
1.3:1	1.4:1	1.5:1	1.7:1	1.9:1	
0.3	0.4	0.5	0.7	0.8	dB
70	60	60	55	50	dB
80	60	50	20	10	Watts
	DC to 6 1.3:1 0.3 70	DC to 6 6 to 12.4  1.3:1 1.4:1  0.3 0.4  70 60	DC to 6         6 to 12.4         12.4 to 18           1.3:1         1.4:1         1.5:1           0.3         0.4         0.5           70         60         60	DC to 6         6 to 12.4         12.4 to 18         18 to 26.5           1.3:1         1.4:1         1.5:1         1.7:1           0.3         0.4         0.5         0.7           70         60         60         55	DC to 6         6 to 12.4         12.4 to 18         18 to 26.5         26.5 to 40           1.3:1         1.4:1         1.5:1         1.7:1         1.9:1           0.3         0.4         0.5         0.7         0.8           70         60         60         55         50

**Electrical Specification Notes:** 

Average Power and Actuating Current values at 25°C.

### **Mechanical Specifications**

Size

 Length
 1.53 in [38.86 mm]

 Width/Diameter
 1.27 in [32.26 mm]

 Height
 1.33 in [33.78 mm]

 Weight
 0.19 lbs [86.18 g]

 Package Type
 Connectorized Module

 Operating Life
 2,500,000 Cycles

 Switching Time
 15 ms Max

Connectors

RF Connector Type 2.92mm Female
RF Connector Specification MIL C 39012
Control Connector Solder Pins

Mechanical Specification Notes: Solder Pins: 250°C max/30sec.

### **Environmental Specifications**

Temperature

Operating Range -40 to +85 deg C Storage Range -55 to +85 deg C

Construction Splashproof

Shock MIL-STD-202, Method 213B, Cond.G

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Transfer Electromechanical Relay Latching Switch DC to 40 GHz, 2.92mm, 10 Watts, 30V Indicator, 28V Control with Indicators, Self Cut Off PE71S6071

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





# **Electromechanical Relay Switches Technical Data**

PE71S6071

Vibration ESD Sensitivity MIL-STD-202, Method 204D, Cond.C ESD Sensitive Material. Transport material in approved ESD bags. Handle in approved ESD Workstation.



Environmental Specification Notes: Environmental specifications are guaranteed but not tested.

Compliance Certifications (visit www.Pasternack.com for current document)
RoHS Compliant
REACH Compliant
12/17/2014

#### **Plotted and Other Data**

Notes:

Values shown are typical at 25°C.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Transfer Electromechanical Relay Latching Switch DC to 40 GHz, 2.92mm, 10 Watts, 30V Indicator, 28V Control with Indicators, Self Cut Off PE71S6071

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451






# **Electromechanical Relay Switches Technical Data**

### PE71S6071

#### **Typical Performance Data**





Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Transfer Electromechanical Relay Latching Switch DC to 40 GHz, 2.92mm, 10 Watts, 30V Indicator, 28V Control with Indicators, Self Cut Off PE71S6071

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





# **Electromechanical Relay Switches Technical Data**

### PE71S6071



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Transfer Electromechanical Relay Latching Switch DC to 40 GHz, 2.92mm, 10 Watts, 30V Indicator, 28V Control with Indicators, Self Cut Off PE71S6071

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





# **Electromechanical Relay Switches Technical Data**

PE71S6071

Transfer Electromechanical Relay Latching Switch DC to 40 GHz, 2.92mm, 10 Watts, 30V Indicator, 28V Control with Indicators, Self Cut Off from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Transfer Electromechanical Relay Latching Switch DC to 40 GHz, 2.92mm, 10 Watts, 30V Indicator, 28V Control with Indicators, Self Cut Off PE71S6071


URL: http://www.pasternack.com/sma-transfer-electromechanical-relay-switch-40-ghz-indicators-pe71s6071-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

# PE71S6071 CAD Drawing

Transfer Electromechanical Relay Latching Switch DC to 40 GHz, 2.92mm, 10 Watts, 30V Indicator, 28V Control with Indicators, Self Cut Off



# PE71S6071 CAD Drawing

Transfer Electromechanical Relay Latching Switch DC to 40 GHz, 2.92mm, 10 Watts, 30V Indicator, 28V Control with Indicators, Self Cut Off

