



SP6T Electromechanical Relay Normally Open Switch DC to 40 GHz, 2.92mm, 3 Watts, 28V Control, Indicators, TTL, Diodes

Electromechanical Relay Switches Technical Data Sheet

PE71S6145

Features

- Single Pole Six Throw Relay Switch
- DC to 40 GHz Frequency Range
- 1M Cycle Min Operating Life
- Normally Open Actuator
- TTL Logic Driver, Position Indicators, Suppression Diodes
- Insertion Loss 1 dB max
- Isolation 50 dB min
- 3 Watts Avg Power Max
- Switching Sequence Break Before Make

Applications

- Test & Measurement
- Communications System
- Instrumentation
- Suitable for Aircraft

Description

The PE71S6145 is a Single Pole Six Throw Electromechanical Relay Switch that operates from DC to 40 GHz and has a rating of 3 Watts input power (CW) in a Break Before Make condition. The design features a Normally Open Actuator with TTL Logic Driver, Position Indicators, Suppression Diodes and is rated for 1M Life Cycles for high reliability operation. Insertion loss is specified from 0.2 dB max and Isolation from 70 dB min, with +28 Vdc operating voltage and performance is guaranteed over -35°C to +85°C. The package interface uses solder terminals and 2.92mm Female connectors.

Electrical Specifications

Switch Type	SP6T, Reflective
Actuator Type	Normally Open
Switching Sequence	Break Before Make
Actuator Options	Indicators, TTL Logic, Diodes
TTL Control	on: 2.4 to 5 Volts off: 0 to 0.8 Volts

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		40	GHz
Impedance		50		Ohms
Operating Voltage	24	28	30	Volts
Actuating Current @ 28 Volts			200	mA
VSWR			2:1	
Insertion Loss			1	dB
Isolation	50			dB
Input Power (CW) (at 40 GHz)			3	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T Electromechanical Relay Normally Open Switch DC to 40 GHz, 2.92mm, 3 Watts, 28V Control, Indicators, TTL, Diodes PE71S6145](#)



SP6T Electromechanical Relay Normally Open Switch DC to 40 GHz, 2.92mm, 3 Watts, 28V Control, Indicators, TTL, Diodes

Electromechanical Relay Switches Technical Data

PE71S6145

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 6	6 to 12	12 to 18	18 to 26.5	26.5 to 40	GHz
VSWR, Max	1.3:1	1.4:1	1.5:1	1.7:1	2:1	
Insertion Loss, Max	0.2	0.4	0.5	0.7	1	dB
Isolation, Min	70	60	60	55	50	dB

Mechanical Specifications

Size

Length 2.25 in [57.15 mm]

Width/Diameter 1.75 in [44.45 mm]

Height 1.75 in [44.45 mm]

Weight 0.284 lbs [128.82 g]

Body Material and Plating Aluminum

Package Type Connectorized Module

Operating Life 1,000,000 Cycles

Switching Time 15 ms Max

Connectors

RF Connector Type 2.92mm Female

RF Connector Specification MIL-C-39012

RF Connector Contact Material and Plating Beryllium Copper, Gold

RF Connector Body Material and Plating Passivated Stainless Steel

Control Connector Solder Pin

Environmental Specifications

Temperature

Operating Range -35 to +85 deg C

ESD Sensitivity ESD Sensitive Material. Transport material in Approved ESD bags. Handle in approved ESD Workstation.



Environmental Specification Notes:
Designed to meet MIL-E-5400 and MIL-S-3928

Compliance Certifications (visit www.Pasternack.com for current document)

Not RoHS Compliant

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T Electromechanical Relay Normally Open Switch DC to 40 GHz, 2.92mm, 3 Watts, 28V Control, Indicators, TTL, Diodes PE71S6145](#)



SP6T Electromechanical Relay Normally Open Switch DC to 40 GHz, 2.92mm, 3 Watts, 28V Control, Indicators, TTL, Diodes


Electromechanical Relay Switches Technical Data

PE71S6145

Plotted and Other Data

Notes:

Typical Performance Data




Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T Electromechanical Relay Normally Open Switch DC to 40 GHz, 2.92mm, 3 Watts, 28V Control, Indicators, TTL, Diodes PE71S6145](#)



SP6T Electromechanical Relay Normally Open Switch DC to 40 GHz, 2.92mm, 3 Watts, 28V Control, Indicators, TTL, Diodes

Electromechanical Relay Switches Technical Data

PE71S6145




SP6T Electromechanical Relay Normally Open Switch DC to 40 GHz, 2.92mm, 3 Watts, 28V Control, Indicators, TTL, Diodes from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP6T Electromechanical Relay Normally Open Switch DC to 40 GHz, 2.92mm, 3 Watts, 28V Control, Indicators, TTL, Diodes PE71S6145](http://www.pasternack.com/2.92mm-sp6t-electromechanical-relay-switch-40-ghz-normally-open-indicators-ttl-logic-pe71s6145-p.aspx)

URL: <http://www.pasternack.com/2.92mm-sp6t-electromechanical-relay-switch-40-ghz-normally-open-indicators-ttl-logic-pe71s6145-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

SP6T Electromechanical Relay Normally Open Switch DC to 40 GHz,
2.92mm, 3 Watts, 28V Control, Indicators, TTL, Diodes



NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES (mm).

DWG TITLE
PE71S6145

FSCM NO. 53919

CAD FILE 040215

SCALE N/A

SIZE A

2233


PE PASTERNAK®
THE ENGINEER'S RF SOURCE

Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623

Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

PE71S6145 CAD Drawing

SP6T Electromechanical Relay Normally Open Switch DC to 40 GHz,
2.92mm, 3 Watts, 28V Control, Indicators, TTL, Diodes



SCHEMATIC SHOWN IN DE-ENERGIZED POSITION

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE
PE71S6145

FSCM NO. 53919

CAD FILE 040215

SCALE N/A

SIZE A

2233

P**E** **PASTERNAK**
THE ENGINEER'S RF SOURCE
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com