



SP4T Electromechanical Relay Switch DC to 22 GHz,
 SMA, 20 Watts, 28V Control with Indicators, TTL

Electromechanical Relay Switches Technical Data Sheet

PE71S6304

Features

- SP4T Absorptive Switch
- DC to 22 GHz Operating Frequency Range
- 1 M Cycles min

Applications

- Test & Measurement
- Communications System
- Instrumentation

Description

The PE71S6304 is a Single Pole Four Throw Absorptive Switch that operates from DC to 22 GHz. The switch has a normally open actuator, an indicator and 1M life cycles. The switch has an operating voltage of 28 Volts and has TTL control.

Electrical Specifications

Switch Type	SP4T, Absorptive
Actuator Type	Normally Open
Switching Sequence	Break Before Make
Actuator Options	Indicators, TTL Logic
TTL Control	on: "High" off: "Low"

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		22	GHz
Impedance		50		Ohms
Operating Voltage		28		Volts
Actuating Current @ 28 Volts		170		mA
VSWR			1.6:1	
Insertion Loss			0.6	dB
Isolation	60			dB
Input Power (CW) (@ 22 GHz)			20	Watts

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 4	4 to 8	8 to 12	12 to 18	18 to 22	GHz
VSWR, Max	1.2:1	1.3:1	1.4:1	1.5:1	1.6:1	
Insertion Loss, Max	0.3	0.35	0.4	0.5	0.6	dB
Isolation, Min	75	70	65	60	60	dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T Electromechanical Relay Switch DC to 22 GHz, SMA, 20 Watts, 28V Control with Indicators, TTL PE71S6304](#)



SP4T Electromechanical Relay Switch DC to 22 GHz,
SMA, 20 Watts, 28V Control with Indicators, TTL

Electromechanical Relay Switches Technical Data

PE71S6304

Mechanical Specifications

Size

Length	2.13 in [54.1 mm]
Width/Diameter	2.13 in [54.1 mm]
Height	2.58 in [65.53 mm]
Weight	0.625 lbs [283.5 g]
Body Material and Plating	Aluminum, Gold

Operating Life	1,000,000 Cycles
Switching Time	15 ms Max

Connectors

RF Connector Type	SMA Female
RF Connector Contact Material and Plating	Beryllium Copper, Gold
RF Connector Body Plating	Passivated Stainless Steel

Environmental Specifications

Temperature

Operating Range	-25 to +65 deg C
-----------------	------------------

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T Electromechanical Relay Switch DC to 22 GHz, SMA, 20 Watts, 28V Control with Indicators, TTL PE71S6304](#)





SP4T Electromechanical Relay Switch DC to 22 GHz,
SMA, 20 Watts, 28V Control with Indicators, TTL

Electromechanical Relay Switches Technical Data

PE71S6304

Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T Electromechanical Relay Switch DC to 22 GHz, SMA, 20 Watts, 28V Control with Indicators, TTL PE71S6304](#)



SP4T Electromechanical Relay Switch DC to 22 GHz,
SMA, 20 Watts, 28V Control with Indicators, TTL

Electromechanical Relay Switches Technical Data

PE71S6304

SP4T Electromechanical Relay Switch DC to 22 GHz, SMA, 20 Watts, 28V Control with Indicators, TTL from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T Electromechanical Relay Switch DC to 22 GHz, SMA, 20 Watts, 28V Control with Indicators, TTL PE71S6304](http://www.pasternack.com/sma-sp4t-electromechanical-relay-switch-22-ghz-indicators-ttl-logic-pe71s6304-p.aspx)

URL: <http://www.pasternack.com/sma-sp4t-electromechanical-relay-switch-22-ghz-indicators-ttl-logic-pe71s6304-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE71S6304 CAD Drawing

SP4T Electromechanical Relay Switch DC to 22 GHz, SMA,
20 Watts, 28V Control with Indicators, TTL



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES.	
DECIMALS	ANGLES
.XX \pm .03 (0.76)	\pm 1°
.XXX \pm .010 (0.254)	FRACTIONS \pm 1/16
HOLE DIAMETER	TOLERANCE
.0135 TO .125 (0.343 TO 3.175)	+0.004 TO -0.001 (+0.102 TO -0.025)
.126 TO .250 (3.200 TO 6.350)	+0.005 TO -0.001 (+0.127 TO -0.025)
.251 TO .500 (6.375 TO 12.700)	+0.006 TO -0.001 (+0.152 TO -0.025)
.501 TO .750 (12.725 TO 19.050)	+0.008 TO -0.001 (+0.203 TO -0.025)
.751 TO 1.000 (19.075 TO 25.400)	+0.010 TO -0.001 (+0.254 TO -0.025)
1.001 TO 2.000 (25.425 TO 50.800)	+0.012 TO -0.001 (+0.305 TO -0.025)

* THESE DIMENSIONS AND TOLERANCES SUPERSEDE NOTE #1 ON TITLE BLOCK.

PE PASTERNAK®
THE ENGINEER'S RF SOURCE
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com


DWG TITLE
PE71S6304

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

FSCM NO. 53919 CAD FILE 090115 SCALE N/A SIZE A 2233

PE71S6304 CAD Drawing

SP4T Electromechanical Relay Switch DC to 22 GHz, SMA,
20 Watts, 28V Control with Indicators, TTL



SCHEMATIC NORMALLY OPEN SHOWN IN DE-ENERGIZED POSITION

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE	PE71S6304		
FSCM NO.	53919	CAD FILE	090115
SCALE	N/A	SIZE	A
			2233

PE PASTERNAK
THE ENGINEER'S RF SOURCE
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com