

SPDT Electromechanical Relay Latching Switch, DC to 18 GHz, 12V, Self Cut Off, Indicators, TTL, Diodes, N



PE71S6594

Features

- Single Pole Double Throw
- DC to 18 GHz Frequency Range
- Isolation greater than 60 dB minimum
- 1M Cycle Min Operating Life
- +12 Volt DC
- 100 Watt average Power
- Latching Self Cut Off Actuator
- TTL Logic Control
- Suppression Diodes
- Indicators
- -25 to +65°C Operating Temperature
- Insertion Loss as low as 0.8 dB Max
- VSWR as low as 1.8:1 max
- N-Type Female RF connectors
- Solder Terminals for DC Control
- Hot Switching Capability - Consult Factory
- S-Parameter Data available upon request

Applications

- Aerospace & Defense
- Test & Measurement
- Microwave Radio Systems
- Military Commercial Communication Systems
- Research & Development
- SATCOM
- Wireless Communications
- Enterprise
- IOT

Description

The PE71S6594 is a Single Pole Double Throw (SPDT) electromechanical relay switch that operates across a wide frequency range of DC to 18 GHz and can handle up to 100 Watts of CW input power in a break before make condition. The 50 Ohm design is rated for 1M life cycles for high reliability operation and features a Latching Self Cut Off actuator, which maintains its position without continuous power, reducing power consumption and ensuring stable operation even during power loss. Additional features include TTL control logic, suppression diodes which limit voltage spikes or reverse current, and indicators. Impressive performance includes insertion loss less than 0.8 dB maximum and isolation greater than 60 dB minimum. The Latching actuator requires +12 Vdc bias voltage, and operates over a temperature range of -25°C to +65°C. The rugged and compact package assembly supports N-Type Female connectors and terminal solder pins for DC Control. And for highly reliable operation, the model is guaranteed to meet MIL-STD-202 environmental test conditions for shock and random vibration.

Electrical Specifications (TA = +25°C, DC Voltage = 12 Vdc)

Switch Type	SPDT
Actuator Type	Latching
Switching Sequence	Break Before Make
Actuator Options	Self Cut Off, Indicators, TTL Logic, Diodes
TTL Control	on: 2.4 to 5 Volts off: 0 to 0.8 Volts 200 mA at 5 Volts 5 mA at 0.8 Volts
TTL Control Current	

Description	Min	Typ	Max	Units
Frequency Range	DC		18	GHz
Impedance	50			Ohms
Operating Voltage	12			Volts
Actuating Current @ 12 Volts			200	mA
VSWR		1.8:1		
Insertion Loss			0.8	dB

SPDT Electromechanical Relay Latching Switch, DC to 18 GHz, 12V, Self Cut Off, Indicators, TTL, Diodes, N



PE71S6594

Description	Min	Typ	Max	Units
Isolation	60			dB
Input Power (CW)		100		Watts
Switching Time			20	ms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 3	3 to 8	8 to 12	12 to 18		GHz
VSWR, Max	1.25:1	1.4:1	1.6:1	1.8:1		
Insertion Loss, Max	0.3	0.4	0.5	0.8		dB
Isolation, Min	80	70	65	60		dB

Electrical Specification Notes:

Average Power for Cold Switching (Reference RF Power Rating Table for Cold Switching)

SPDT Electromechanical Relay Latching Switch, DC to 18 GHz, 12V, Self Cut Off, Indicators, TTL, Diodes, N



PE716594

Mechanical Specifications

Size

Length	2.75 in [69.85 mm]
Width/Diameter	2.36 in [59.94 mm]
Height	0.92 in [23.37 mm]
Weight	0.05 lbs [22.68 g]
Package Type	Connectorized
Operating Life	1,000,000 Cycles

Connectors

RF Connector Type	N Female
Control Connector	Solder Pin

Mechanical Specification Notes:

Solder Pins: 250°C max/5sec.

Environmental Specifications

Temperature

Operating Range	-25 to +65 deg C
Construction	Splashproof
Shock	MIL-STD-202 Method 213, Condition D (500G Non Operating)
Vibration	MIL-STD-202 Method 214, Condition D (10G RMS Non Operating)

Compliance Certifications

 (see product page for current document)

Plotted and Other Data

Notes:



Values shown are typical at 25°C.

SPDT Electromechanical Relay Latching Switch, DC to 18 GHz, 12V, Self Cut Off, Indicators, TTL, Diodes, N



PE71S6594

Typical Performance Data



Power handling chart and derating curves based on the following conditions:

- Ambient temperature: 40°C or less
- Altitude: Sea level
- Load VSWR: 1.20:1 Maximum
- Relative Humidity: 40-50%
- Cold switching: RF signal off

Note: specifications subject to change without notice

SPDT Electromechanical Relay Latching Switch, DC to 18 GHz, 12V, Self Cut Off, Indicators, TTL, Diodes, N



PE71S6594

SPDT Electromechanical Relay Latching Switch, DC to 18 GHz, 12V, Self Cut Off, Indicators, TTL, Diodes, N from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SPDT Electromechanical Relay Latching Switch, DC to 18 GHz, 12V, Self Cut Off, Indicators, TTL, Diodes, N PE71S6594](https://www.pasternack.com/spdt-electromechanical-relay-latching-switch-18-ghz-12v-indicators-ttl-diodes-n-pe71s6594-p.aspx)

URL: <https://www.pasternack.com/spdt-electromechanical-relay-latching-switch-18-ghz-12v-indicators-ttl-diodes-n-pe71s6594-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE71S6594 CAD Drawing

SPDT Electromechanical Relay Latching Switch, DC to 18 GHz, 12V, Self Cut Off, Indicators, TTL, Diodes, N

