



78 Ohm TRS Plug 1553 Connector Crimp/
Solder Attachment for M17/176-00002,

RF Connectors
Technical Data Sheet

PE410-10030-206

Configuration

- TRS Plug Connector
- MIL-STD-1553
- 78 Ohms
- Straight Body Geometry
- Connector Interface Types: M17/176-00002, TRS PLUG
- 1553 Design

Features

- Max. Operating Frequency 500 MHz
- Gold 30 micro inches Plated Bronze Contact
- Contact plating according to ASTM-B-488

Applications

- General Purpose Test
- Custom Cable Assemblies
- M17/176-00002

Description

TRS SUBMINIATURE 3-SLOT CABLE PLUG for twinaxial cable M17/176-00002.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		500	MHz
Impedance		78		Ohms

Mechanical Specifications

Size	
Length	0.76 in [19.20 mm]
Width	0.45 in [11.50 mm]
Height	0.45 in [11.50 mm]
Weight	0.01 lbs [4.54 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [78 Ohm TRS Plug 1553 Connector Crimp/Solder Attachment for M17/176-00002, PE410-10030-206](#)



78 Ohm TRS Plug 1553 Connector Crimp/
Solder Attachment for M17/176-00002,

RF Connectors Technical Data Sheet

PE410-10030-206

Material Specifications

Description	Material	Plating
Contact	Bronze	Gold 30 micro inches ASTM-B-488
Insulation	Teflon	
Outer Conductor	Phosphor Bronze	Gold 30 micro inches ASTM-B-488
Body	Brass	Nickel ASTM-B-733
Gasket	Rubber	
Crimp Sleeve	Brass	Nickel

Environmental Specifications

Temperature

Operating Range -55 to +200 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

78 Ohm TRS Plug 1553 Connector Crimp/Solder Attachment for M17/176-00002, from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [78 Ohm TRS Plug 1553 Connector Crimp/Solder Attachment for M17/176-00002, PE410-10030-206](#)

URL: <https://www.pasternack.com/plug-m17-176-00002-connector-pe410-10030-206-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE410-10030-206 CAD Drawing

78 Ohm TRS Plug 1553 Connector Crimp/Solder Attachment for M17/176-00002,



Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920

DESCRIPTION
TRS SUBMINIATURE 3-SLOT PLUG

SCALE	NONE
SHEET	1 OF 1
ITEM NO.	PE410-10030

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

X = ± .2	[.5]	FRACTIONS
.XX = ± .02	[.13]	± 1/32
.XXX = ± .005	[.13]	ANGLES ± 1°

CABLE LENGTH TOLERANCES:

≤ 12 [305]	± .125 [-0]
> 12 [305]	± .60 [1524] = +2 [51] / -0
> 60 [1524]	± 120 [3048] = +4 [102] / -0
> 120 [3048]	± 300 [7620] = +6 [152] / -0
> 300 [7620]	± .5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE