


50 dB Fixed Attenuator, SMA Male to TNC  
Female Black Anodized Aluminum Heatsink  
Body Rated to 25 Watts Up to 8 GHz



## PE7358-50

### Features

### Applications

### Description

Pasternack carries a wide range of fixed attenuators with a broad selection of attenuation levels, frequency ranges, and power dissipation ranges. RF microwave attenuators (also known as RF pads) lower the amplitude of a signal (attenuate) a known amount and can be used in a wide variety of applications. These attenuator pads are used when a signal needs to be reduced to protect measurement equipment or other circuitry, to extend the range of power meters and amplifiers, and to impedance match circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Pasternack carries one of the largest in-stock varieties and ships them same day. The 50 dB Fixed Attenuator PE7358-50 is rated to 25 Watts and operates from DC to 8 GHz. The versatile coaxial package uses SMA male to TNC female connectors and is also REACH and RoHS compliant. The Black Anodized Aluminum Heatsink body allows for efficient heat dissipation under high power usage conditions.

### Electrical Specifications

| Description         | Minimum | Typical | Maximum | Units |
|---------------------|---------|---------|---------|-------|
| Frequency Range     | DC      |         | 8       | GHz   |
| Impedance           |         | 50      |         | Ohms  |
| Nominal Attenuation |         | 50      |         | dB    |
| VSWR                |         |         | 1.6:1   |       |
| Input Power, CW     |         |         | 25      | Watts |
| Input Power, Peak   |         |         | 500     | Watts |

### Specifications by Frequency


| Description               | F1      | F2     | F3 | F4 | F5 | Units |
|---------------------------|---------|--------|----|----|----|-------|
| Frequency Range           | DC to 6 | 6 to 8 |    |    |    | GHz   |
| VSWR, Max                 | 1.3:1   | 1.45:1 |    |    |    |       |
| Attenuation Accuracy, Typ | 0.5     |        |    |    |    | dB    |
| Input Power, CW           | 25      |        |    |    |    | Watts |

### Mechanical Specifications

#### Size

|                           |                                  |
|---------------------------|----------------------------------|
| Length                    | 4.5 in [114.3 mm]                |
| Width/Diameter            | 2.41 in [61.21 mm]               |
| Height                    | 0 in [0 mm]                      |
| Weight                    | 0.8 lbs [362.87 g]               |
| Body Material and Plating | Black Anodized Aluminum Heatsink |

50 dB Fixed Attenuator, SMA Male to TNC  
Female Black Anodized Aluminum Heatsink  
Body Rated to 25 Watts Up to 8 GHz



## PE7358-50

### Configuration

Design Fixed, Bidirectional

### Connectors

| Description                          | Connector 1                 | Connector 2                 |
|--------------------------------------|-----------------------------|-----------------------------|
| Type                                 | SMA Male                    | TNC Female                  |
| Contact Material and Plating         | Beryllium Copper, Gold      | Beryllium Copper, Gold      |
| Contact Plating Specification        | Gold                        |                             |
| Outer Conductor Material and Plating |                             | Stainless Steel, Passivated |
| Coupling Nut Material and Plating    | Stainless Steel, Passivated |                             |
| Coupling Nut Plating Specification   | Stainless Steel             |                             |
| Hex Size                             | 11/16 In.                   | 11/16 In.                   |
| Body Material and Plating            | Stainless Steel, Passivated | Stainless Steel, Passivated |
| Body Plating Specification           | Passivated                  |                             |

### Environmental Specifications

#### Temperature

Operating Range -55 to +125 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

### Typical Performance Data

50 dB Fixed Attenuator, SMA Male to TNC Female Black Anodized Aluminum Heatsink Body Rated to 25 Watts Up to 8 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [50 dB Fixed Attenuator, SMA Male to TNC Female Black Anodized Aluminum Heatsink Body Rated to 25 Watts Up to 8 GHz PE7358-50](#)

URL: <https://www.pasternack.com/50db-fixed-sma-male-tnc-female-25-watts-attenuator-pe7358-50-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE7358-50 CAD Drawing

50 dB Fixed Attenuator, SMA Male to TNC Female Black Anodized Aluminum Heatsink Body Rated to 25 Watts Up to 8 GHz

