

## 10 dB Fixed Attenuator, 2.92mm Male to 2.92mm Female Black Anodized Aluminum Body Rated to 20 Watts Up to 40 GHz



### PE7513-10

#### Features

- DC to 40 GHz Range
- Attenuation 10±1.5 dB
- 20 Watts Average Input Power
- VSWR <1.4:1

#### Applications

- Precision Measurements
- Production Systems
- Instrumentation
- Prototyping and Characterization
- 5G and 6G Communications

#### Description

Pasternack carries a wide range of fixed attenuators with a broad selection of attenuation levels, frequency ranges, and power dissipation ranges. RF microwave attenuators (also known as RF pads) lower the amplitude of a signal (attenuate) a known amount and can be used in a wide variety of applications. These attenuator pads are used when a signal needs to be reduced to protect measurement equipment or other circuitry, to extend the range of power meters and amplifiers, and to impedance match circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Pasternack carries one of the largest in-stock varieties and ships them same day. The 10 dB Fixed Attenuator PE7513-10 is rated to 20 Watts and operates from DC to 40 GHz. The versatile coaxial package uses 2.92mm male to 2.92mm female connectors.

#### Electrical Specifications

| Description                                             | Minimum | Typical | Maximum | Units |
|---------------------------------------------------------|---------|---------|---------|-------|
| Frequency Range                                         | DC      |         | 40      | GHz   |
| Impedance                                               |         | 50      |         | Ohms  |
| Nominal Attenuation                                     |         | 10      |         | dB    |
| Attenuation Accuracy                                    |         | ±1.5    | ±3      | dB    |
| VSWR                                                    |         |         | 1.4:1   |       |
| Input Power, CW                                         |         |         | 20      | Watts |
| 25°C ambient temperature, derated linearly to 2W @125°C |         |         |         |       |
| Input Power, Peak                                       |         |         | 200     | Watts |
| 5 µSec PW, 10% duty cycle                               |         |         |         |       |

#### Mechanical Specifications

##### Size

|                           |                         |
|---------------------------|-------------------------|
| Length                    | 3.15 in [80.01 mm]      |
| Width/Diameter            | 1.5 in [38.1 mm]        |
| Height                    | 1.5 in [38.1 mm]        |
| Weight                    | 0.18 lbs [81.65 g]      |
| Body Material and Plating | Black Anodized Aluminum |

##### Configuration

|             |                       |
|-------------|-----------------------|
| Design      | Fixed, Unidirectional |
| Design Type | Standard              |

10 dB Fixed Attenuator, 2.92mm Male to  
2.92mm Female Black Anodized Aluminum  
Body Rated to 20 Watts Up to 40 GHz



## PE7513-10

| Package Style                | Connectorized          |                        |
|------------------------------|------------------------|------------------------|
| Connectors                   |                        |                        |
| Description                  | Connector 1            | Connector 2            |
| Type                         | 2.92mm Male            | 2.92mm Female          |
| Contact Material and Plating | Beryllium Copper, Gold | Beryllium Copper, Gold |
| Body Material and Plating    | Stainless Steel        | Stainless Steel        |

### Environmental Specifications

**Temperature**

Operating Range -55 to +100 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

### Typical Performance Data

10 dB Fixed Attenuator, 2.92mm Male to 2.92mm Female Black Anodized Aluminum Body Rated to 20 Watts Up to 40 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [10 dB Fixed Attenuator, 2.92mm Male to 2.92mm Female Black Anodized Aluminum Body Rated to 20 Watts Up to 40 GHz PE7513-10](#)

URL: <https://www.pasternack.com/10db-fixed-2.92mm-male-2.92mm-female-20-watts-attenuator-pe7513-10-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE7513-10 CAD Drawing

10 dB Fixed Attenuator, 2.92mm Male to 2.92mm Female Black Anodized Aluminum Body Rated to 20 Watts Up to 40 GHz

