

6 dB Fixed Attenuator SMA Male to SMA  
Female Black Anodized Aluminum Heatsink  
Body Rated 10 Watt DC to 18 GHz



**PE7626-6**

**Features**

- DC to 18 GHz Frequency Range
- SMA Connectorized Design
- Attenuation 6 dB  $\pm$ 0.8 dB
- Max Power 5 Watts (CW)
- Max VSWR of 1.3:1

**Applications**

- Instrumentation
- Precision Measurements
- Prototyping and Characterization
- Production Systems

**Description**

Pasternack carries a wide range of fixed attenuators with a broad selection of attenuation levels, frequency ranges, and power dissipation ranges. RF microwave attenuators (also known as RF pads) lower the amplitude of a signal (attenuate) a known amount and can be used in a wide variety of applications. These attenuator pads are used when a signal needs to be reduced to protect measurement equipment or other circuitry, to extend the range of power meters and amplifiers, and to impedance match circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Pasternack carries one of the largest in-stock varieties and ships them same day. The 6 dB Fixed Attenuator PE7626-6 is rated to 10 Watts and operates from DC to 18 GHz. The versatile coaxial package uses SMA male to SMA female connectors and is also REACH compliant.

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
Impedance		50		Ohms
Nominal Attenuation		6		dB
Attenuation Accuracy		$\pm$ 0.8		dB
VSWR			1.3:1	
Input Power, CW			10	Watts
Derated linearly to 1W @ 125°C				
Input Power, Peak			500	Watts
5 $\mu$ Sec PW, 2% duty cycle				

**Mechanical Specifications**

**Size**

Length	1.89 in [48.01 mm]
Width/Diameter	0.65 in [16.51 mm]
Height	0.65 in [16.51 mm]
Weight	0.01 lbs [4.54 g]
Body Material and Plating	Black Anodized Aluminum

**Configuration**

Design	Fixed, Unidirectional
Package Style	Connectorized

6 dB Fixed Attenuator SMA Male to SMA  
Female Black Anodized Aluminum Heatsink  
Body Rated 10 Watt DC to 18 GHz



## PE7626-6

### Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SMA Female
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold
Body Material and Plating	Brass, Nickel	Brass, Nickel

### Environmental Specifications

#### Temperature

Operating Range -55 to +125 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

### Typical Performance Data

6 dB Fixed Attenuator SMA Male to SMA Female Black Anodized Aluminum Heatsink Body Rated 10 Watt DC to 18 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [6 dB Fixed Attenuator SMA Male to SMA Female Black Anodized Aluminum Heatsink Body Rated 10 Watt DC to 18 GHz PE7626-6](#)

URL: <https://www.pasternack.com/6db-fixed-sma-male-sma-female-10-watts-attenuator-pe7626-6-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE7626-6 CAD Drawing

6 dB Fixed Attenuator SMA Male to SMA Female Black Anodized Aluminum Heatsink Body Rated 10 Watt DC to 18 GHz

