

DC Block on Inner and Outer Conductor 50 Ohm BNC Male to BNC Female Operating From 100 MHz to 4 GHz



PE8218A

Features

- Inner/Outer DC Blocks
- BNC Connectorized Configuration
- 100 MHz to 4 GHz Frequency Range
- 50 Ohm Impedance
- Max VSWR of 1.35:1

Applications

- Test and Measurement
- Ground Loop Elimination
- Signal to Noise Ratio (SNR) Improvement

Description

Pasternack's PE8218A is an inner and outer DC block with BNC connectors. It has a blocking capacitor on the inner and outer conductor and operates from 100 MHz to 4 GHz. Our BNC DC block offers good insertion loss of 0.5 dB and has a maximum operating voltage of 200 Vdc. DC blocks are commonly used to filter out unwanted DC signals, while allowing AC drive signals to pass through. They can help improve signal to noise ratio (SNR), eliminate ground loops, or provide isolation in your test setup. All of Pasternack's DC blocks are in stock and available to ship same-day.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	0.1		4	GHz
Impedance		50		Ohms
VSWR			1.35:1	
Insertion Loss			0.5	dB
Operating Voltage (DC)			200	Volts

Mechanical Specifications

Size

Length	2.09 in [53.09 mm]
Width	0.57 in [14.48 mm]
Height	0.57 in [14.48 mm]
Weight	0.04 lbs [18.14 g]
Housing Material and Plating	Brass, Copper-Tin-Zinc Alloy

Configuration

Design	Inner/Outer DC Block
--------	----------------------

Description	Connector 1	Connector 2
Type	BNC Male	BNC Female
Inner Cond Material & Plating	Beryllium Copper, Gold over Nickel over Copper	Beryllium Copper, Gold over Nickel over Copper
Dielectric Type	Teflon	Teflon
Body Material & Plating	Brass, Copper-Tin-Zinc Alloy	Brass, Copper-Tin-Zinc Alloy

DC Block on Inner and Outer Conductor 50 Ohm BNC
Male to BNC Female Operating From 100 MHz to 4 GHz



PE8218A

Environmental Specifications

Temperature

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data

DC Block on Inner and Outer Conductor 50 Ohm BNC Male to BNC Female Operating From 100 MHz to 4 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [DC Block on Inner and Outer Conductor 50 Ohm BNC Male to BNC Female Operating From 100 MHz to 4 GHz PE8218A](#)

URL: <https://www.pasternack.com/50-ohm-bnc-inner-outer-dc-block-100-mhz-4-ghz-pe8218a-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE8218A CAD Drawing

DC Block on Inner and Outer Conductor 50 Ohm BNC Male to BNC Female Operating From 100 MHz to 4 GHz

