

BMA Jack Connector Crimp Attachment 2 Hole Flange Mount for LMR-100A, PE-B100, PE-C100, RG174, RG174MN, RG316, RG188, LMR-100A-PV



PE5154

Configuration

- BMA Jack Connector
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: LMR-100A, PE-B100, PE-C100, RG174, RG174MN, RG316, RG188, PE-C100-LSZH, LMR-100-FR, LMR-100A-PVC
- 2 Hole Flange

Features

- Max. Operating Frequency 12.4 GHz
- Excellent VSWR of 1.2:1
- Gold over Nickel over Copper Plated Brass Contact
- Blind Mate Connector

Applications

- General Purpose Test
- Rack and Panel Mount Applications
- Custom Cable Assemblies

Description

Pasternack's PE5154 , BMA, Standard, Connector is part of our full line of RF components available for same-day shipping. Our BMA jack connector operates up to a maximum frequency of 12.4 GHz and offers excellent VSWR of 1.2:1. The Pasternack blind mate connector is ideal for applications where direct visual or tactile access to the connection point is not possible, for example, when two circuit boards need to be mated. This BMA 2 hole flange connector allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Our BMA jack 2 hole flange connector PE5154 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12.4	GHz
VSWR			1.2:1	
Insertion Loss			0.105	dB
Operating Voltage (AC)			670	Vrms
Dielectric Withstanding Voltage (AC)			1,000	Vrms
Inner Conductor DC Resistance			2	mOhms
Outer Conductor DC Resistance			2	mOhms
Insulation Resistance	5,000			MOhms
Impedance		50		Ohms

Mechanical Specifications

Size

Length	0.85 in [21.59 mm]
Width	0.752 in [19.1 mm]
Height	0.752 in [19.1 mm]
Weight	0.0146 lbs [6.62 g]

BMA Jack Connector Crimp Attachment 2 Hole Flange Mount for LMR-100A, PE-B100, PE-C100, RG174, RG174MN, RG316, RG188, LMR-100A-PV



PE5154

Material Specifications

Description	Material	Plating
Contact	Brass	Gold over Nickel over Copper
Insulation	PTFE	
Body	Brass	Copper-Tin-Zinc Alloy
Washer	Stainless Steel	

Environmental Specifications

Temperature

Operating Range

-65 to +165 deg C

Humidity

MIL-STD-202, Method 106

Thermal Shock

MIL-STD-202, Method 107, Condition B

Salt Spray

MIL-STD-202, Method 101, Condition B

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

BMA Jack Connector Crimp Attachment 2 Hole Flange Mount for LMR-100A, PE-B100, PE-C100, RG174, RG174MN, RG316, RG188, LMR-100A-PV from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BMA Jack Connector Crimp Attachment 2 Hole Flange Mount for LMR-100A, PE-B100, PE-C100, RG174, RG174MN, RG316, RG188, LMR-100A-PV PE5154](#)

URL: <https://www.pasternack.com/bma-jack-lmr-100a-pe-b100-rg174-rg174mn-rg316-connector-pe5154.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE5154 CAD Drawing

BMA Jack Connector Crimp Attachment 2 Hole Flange Mount for LMR-100A, PE-B100, PE-C100, RG174, RG174MN, RG316, RG188, LMR-100A-PV

